



What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)

HFW1201G01P Product Details

[Share](#)[Print](#)[Email](#)**Active**[View 3D PDF](#)

Military/Aerospace High Performance Relays

HFW1201G01P = M39016/6-116P

HFW1201G01P (M39016/6-116P)

TE Internal Number: 2-1617030-8

Product Highlights [View All](#)

- HFW Half-Size Relay Series
- Input Voltage = 12 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 2 A
- Non Polarized, Monostable Coil - Magnetic System

[Pricing & Availability](#)[Request Sample](#)[Add to My Part List](#)[Buy Product through Distributor](#)[Documents](#)[Features](#)[Compliance](#)**Please Note:**

Use the Product Drawing for all design activity

Product Type Features

MOSFET Driver	Without
---------------	---------

Mechanical Attachment

Mounting Options	PC Board
------------------	----------

Electrical Characteristics

Input Voltage (VDC)	12
Contact - Rated Current (A)	2
Coil Suppression Diode	Without
Coil Polarity Protection Diode	Without
Coil - Resistance (Ω)	160
Coil Power Measurement	Milliwatts
Coil - Rated Power, DC (mW)	900
Actuating System	DC
Shock	100 G's, 6ms
Vibration	30 G's, 10 to 3000Hz

Termination Features**Body Features**

Enclosure Type	Hermetically Sealed
----------------	---------------------

Configuration Features

Contact - Arrangement	2 Form C, DPDT, 2 C/O
Coil - Magnetic System	Non Polarized, Monostable
Transistor Driver	Without

Industry Standards

Government/Industry Qualification	Yes
Government/Industry Part Number	M39016/6-116P
RoHS/ELV Compliance	Not ELV/RoHS compliant
Lead Free Solder Processes	Not suitable for lead free processing
Approved Standards	M39016 Qualified, P Level

Conditions for Usage

Termination Type	PC Pins	Temperature Range (°C)	-65 - +125
Other			
Series	HFW Half-Size Relay		
Brand	CII		

Related Products

Not quite the product
you're looking for?

[Find Similar Products](#)

[View Part in Product Feature
Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms of Use of TE.com](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)
- [Terms & Conditions of Sale](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

