



**Part Number :** [2153431223](#)  
**Product Description :** Pre-Crimped Lead Mini-Fit Jr.  
Male-to-Pigtail, Gold (Au) Plating, 225.00mm Length, 16  
AWG, Black  
**Series Number :** 215343  
**Status :** Active  
**Product Category :** Power and Signal Cable  
Assemblies

## Documents and Resources

**Drawings**  
[2153431223 sd.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                                      |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)                                                          |
| EU RoHS            | Compliant per EU 2015/863                                                                               |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|                        |                                                                                                  |
|------------------------|--------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                           |
| Category               | Power and Signal Cable Assemblies                                                                |
| Series                 | 215343                                                                                           |
| Description            | Pre-Crimped Lead Mini-Fit Jr. Male-to-Pigtail, Gold (Au) Plating, 225.00mm Length, 16 AWG, Black |
| Application            | Power, Wire-to-Wire                                                                              |
| Assembly Configuration | Pre-crimped Lead Only                                                                            |
| Connector to Connector | Mini-Fit Jr. Term-to-Pigtail                                                                     |
| Keyword                | Pre-Crimped Leads                                                                                |
| Product Name           | Mini-Fit Jr.                                                                                     |
| UPC                    | 193264560462                                                                                     |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 9.0A |
| Voltage - Maximum             | 600V |

**Physical**

|                                |              |
|--------------------------------|--------------|
| Cable Length                   | 225.00mm     |
| Circuits (Loaded)              | 1            |
| Circuits (maximum)             | 1            |
| Color - Resin                  | Black        |
| Gender                         | Male-Pigtail |
| Material - Metal               | Brass        |
| Material - Plating Mating      | Gold         |
| Material - Plating Termination | Tin          |
| Net Weight                     | 5.330/g      |
| Packaging Type                 | Bag          |

|                             |                      |
|-----------------------------|----------------------|
| Single Ended                | Yes                  |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type             | UL 1015              |
| Wire Size (AWG)             | 16                   |

## Mates With / Use With

### Use with Part(s)

| Description                         | Part Number  |
|-------------------------------------|--------------|
| Mini-Fit Jr. Plug Housings          | <u>5559</u>  |
| Mini-Fit BMI Dual Row Plug Housings | <u>42475</u> |

---

This document was generated on Jun 04, 2026