Please do not use this product for new DesignIns anymore. Please contact your local distribution partner.

Pushing Performance
Since 1945

# Hinged frame 24B for 6 modules (A..F)




Image is for illustration purposes only. Please refer to product description.

| | |
|---|---|
| Part number | 09 14 024 0303 |
| Specification | Hinged frame 24B for 6 modules (A..F) |
| HARTING eCatalogue | https://harting.com/09140240303 |

## Identification

| | |
|---|---|
| Category | Accessories |
| Series | Han-Modular® |
| Type of accessory | Hinged frame |
| Description of the accessory | for 6 modules<br>A ... F |
| Features | Conductor cross-section PE (power side) 4 ... 10 mm²<br>Conductor cross-section PE (signal side) 1 ... 2.5 mm² |

## Version

| | |
|---|---|
| Size | 24 B |

## Technical characteristics

| | |
|---|---|
| Stripping length | 8 ... 10 mm |
| Tightening torque | 0.8 Nm PE screw M3<br>1.2 Nm PE screw M4 |
| Recommended screw driver | Slotted 0.6 x 3.5<br>PH2 |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

## Material properties

| | |
|---|---|
| Material | Zinc die-cast |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

## Material properties

| | |
|---|---|
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | 564b7d75-7bf6-4cfb-acb1-2168eb61b675 |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead<br>Nickel |

## Specifications and approvals

| | |
|---|---|
| Specifications | IEC 60664-1<br>IEC 61984<br>IEC 61373 Category 2 |
| UL / CSA | UL 1977 ECBT2.E235076 |
| Approvals | DNV GL |

## Commercial data

| | |
|---|---|
| Packaging size | 2 |
| Net weight | 78.3 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140021273 |
| eCl@ss | 27440206 Module carrier frame for industrial connectors |
| ETIM | EC002312 |
| UNSPSC 24.0 | 39121421 |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.