



What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Input/Output (Box to Box) > Product Feature Selector > Product Details

2227250-1 Product Details

Share Print Email



2227250-1

TE Internal Number: 2227250-1



Pluggable Connectors, Cages & Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- zQSFP+ Product Line
- Cage
- zQSFP+ Application
- Cage Type = Ganged
- For Use With Pluggable QSFP Transceivers

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Feedback

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> None Available <p>CAD Files:</p> <ul style="list-style-type: none"> None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> Product Line = zQSFP+ Product Type = Cage <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> PCB Mount = Double Sided (Belly-to-Belly) Bezel Mounting Style = Behind Bezel <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> Data Signal Rate (Gb/s) = Up to 100 <p>Termination Features:</p> <ul style="list-style-type: none"> Termination Method to PC Board = Through Hole - Press Fit <p>Dimensions:</p> <ul style="list-style-type: none"> Tail Length (mm [in]) = 2.2 [0.087] <p>Housing Features:</p> <ul style="list-style-type: none"> Cage Type = Ganged 	<p>Configuration Features:</p> <ul style="list-style-type: none"> Port Configuration = 1x4 Heat Sink Included = No Lightpipe = Without EMI Containment = Internal Springs <p>Industry Standards:</p> <ul style="list-style-type: none"> RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> For Use With = Pluggable QSFP Transceivers Applies To = Printed Circuit Board <p>Operation/Application:</p> <ul style="list-style-type: none"> Application = zQSFP+ Heat Sink Application = Yes <p>Other:</p> <ul style="list-style-type: none"> Brand = TE Connectivity

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

