



YBM25L2, Uninsulated Flag-Type Ring Terminal For 1/0 AWG

By Burndy
Catalog # [YBM25L2](#)



Uninsulated Flag-Type Ring Terminal For 1/0 AWG.

Features

- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

General

Catalog Number	YBM25L2
Connector Type	Flag Ring Terminal
Die Index	58
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810026212
UPC 14 Digit GTIN	00781810026212

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Length Overall inch	1.56 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Pad Width inch	0.72 in
Dimension - Strip Length inch	3/4
Dimension - Stud Size inch	5/16
Dimension - Z (inch)	0.45 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24)
Conductor - Copper Flex I Size	1/0
Conductor - Copper Str Aircraft Size	AN 1/0
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0 AWG
Conductor Size	1/0 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	29400

Product Assets

[3D Models - YBM25L2_MODEL-IGES](#)
[3D Models - YBM25L2_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094169](#)
[Specifications - YBM25L2](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YBM25L2-SPEC-EN | REV 7/2025