



PRODUCT N°	NBR OF CONTACTS	POLARIZING PLUG		DIM"C"	DIM"D"	CONTACT PLACED IN CAVITY (TABLE ACCORDING WITH VIEW "A")																	
						1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
89852-Y01LF	12		TOP TER.	27.94	30.40	X	X	X	X	X	X	X	X	X	X	X	X						
	11	WITHOUT	BOTTOM TER.			X	X	X	X	X	X	X	X	X	X	X	X						
89852-Y02LF	12		TOP TER.	27.94	30.40	X	X	X	X	X	X	X	X	X	X	X	X						
	11	65307-001	BOTTOM TER.			X	X	X	X	X	X	X	X	X	X	X	X						
89852-Y03LF	13	WITHOUT	TOP TER.	43.18	45.64	X	X		X		X		X		X	X	X	X	X	X			
	13	WITHOUT	BOTTOM TER.			X	X		X		X		X		X	X	X	X	X	X			
89852-Y04LF	5		TOP TER.	10.16	12.62	X	X	X	X	X													
	4	WITHOUT	BOTTOM TER.			X			X	X	X												

RoHS COMPATIBLE, SEE NOTE 4

VIEW "A"

SECTION PP



NOTES:

RECOMMENDED HOLE PATTERN

- MATERIAL HOUSING: THERMOPLASTIC POLYESTER, 30% GLASS FILLED, COLOUR BLUE. FLAME RETARDANT PER UL-94 CATEGORY V0.
- MATERIAL TERMINAL: PHOSPHOR BRONZE.
- TERMINALS CAN ONLY BE USED FOR P.C. BOARD APPLICATION WITH THROUGH HOLES.
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - LEGAL STATEMENT: SEE GS-47-0004

89852-4XXLF	Sn	Sn
89852-3XXLF	0.76µm GOLD	Sn
PLATING CODE	CONTACT AREA	SOLDER TAIL
	PLATING THICKNESS OVER 1.27µm Ni MIN	

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 486 ISO 1011	projection mm	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified	angles	linear	File
K	B-20026	BVE	15.01.20	±0.3			DUBOX HCC
L	B-20689	BVE	15.04.15				SELECTED LOADED
F	F04-0366	DLE	04.11.08	dr	P.NIZZI	96.09.24	dwg no
G	F06-0204	DLE	06.06.21	engr	JM PHAMVAN	96.09.24	sheet 1 of 1
H	F07-0271	LMU	07.12.06	chr	P.NIZZI	96.09.24	size
J	B-19123	LMU	14.10.21	appd	JMP	96.09.24	A2
sheet index	revision	sheet					type
							customer
							Drawing