


Home > Products > Power Products (>10 Amps/Contact) > Product Feature Selector > Product Details

5223964-6 Product Details

 Share

 Print

 Email



5223964-6

TE Internal Number: 5223964-6

 Active

 View 3D PDF

Universal Power Modules

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Header
- Connector Style = Plug
- Contact Type = Blade
- 3 Positions

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ASSEMBLY, RIGHT ANGLE HEADER, W/ RETENTION PEGS, UNI... (PDF, English) Catalog Pages/Data Sheets: 2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1 (PDF, English) Product Specifications: - None Available Application Specifications: Universal Power Module (UPM) Connectors (PDF, English) Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version O) 3D Model (IGES, Version O) 3D Model (STEP, Version O) List all Documents	Additional Information: Product Line Information Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Product Type = Connector Connector Type = Header PCB Mounting Orientation = Right Angle Keyed = No Post Type = Compliant Post Dimensions: Mating Post Length (Row A) (mm [in]) = 9.30 [0.366] Mating Post Length (Row B) (mm [in]) = 10.90 [0.429] Mating Post Length (Row C) (mm [in]) = 7.68 [0.302] Contact Features: Contact Type = Blade Solder Tail Contact Plating = Tin Contact Base Material = Phosphor Bronze Contact Plating, Mating Area, Material = Gold (50)	Housing Features: Connector Style = Plug Housing Material = LCP - GF (Liquid Crystal Polymer) Housing Color = Natural Configuration Features: Number of Positions = 3 Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process RoHS/ELV Compliance History = Always was RoHS compliant Other: Brand = AMP Comment = Number 1 marking.; Contact area lubricated with Belcore approved lubricant.

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

