

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date BY - ALL RIGHTS RESERVED.


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	18SEP17	JL	IY
	A1	ECN-22-186507	24NOV22	L.Y	E.J
	A2	ECN-23-224805	02AUG2023	L.Y	E.J
	A3	ECN-24-284155	11SEP2024	N.L	E.J




A-A









A-A







2310488-1




2310488-2



2310488-3



1-231048-1



2-231048-2

NOTES

1 THIS PART IS UL94 V0 VERSION AND RELATED HB VERSION REFER TO TE DRAWING 2141155

2 PACKAGING: BULK PACKAGING IN PLASTIC BAG AND CORRUGATED SHIPPING BOX

PART NO	DIM. A	FOR WIRE SIZE [mm2]	MATERIAL	DESCRIPTION	WEIGHT (g)	SURFACE COLOR
2-2310488-2	11.4	35 UNSHIELDING	PA66-GF UL94 V0	PROTECTION COVER	(3.7)	ORANGE
1-2310488-1	13.6	50 UNSHIELDING	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
2310488-3	12.6	25	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
2310488-2	14.8	35	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
2310488-1	16.2	50	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3, 1 PLC ±, 2 PLC ±, 3 PLC ±, 4 PLC ±, ANGLES 45°

MATERIAL SEE TABLE

FINISH -

DWN JLI 12SEP2017
CHK E.JIANG 15SEP2017
APVD I.YIN 18SEP2017

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

TE Connectivity

NAME PROTECTION COVER

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2310488	

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV A3

4805 (3/13)

Downloaded from Arrow.com.