

External 240V Tower Battery Pack for select Tripp Lite UPS Systems (BP240V500C)

MODEL NUMBER: **BP240V500C**



Highlights

- Extends runtime of compatible Tripp Lite UPS Systems using 240VDC configuration
- Includes built in 7A charger
- Hardwire installation
- Internal DC disconnect
- 10 year design lifespan
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Description

Tripp Lite's BP240V500C External Battery Pack with built-in 7A charger offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Includes 15-ft. (4.57 m) cable to connect to UPS or additional battery pack.

COMPATIBLE UPS SYSTEMS: SU20K3/3, SU30K3/3 and other Tripp Lite UPS systems specifying the use of this battery pack

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Multiple battery packs can be daisy-chained through each other to the UPS for even longer extended run operation
- 15-ft. (4.57 m) DC cable connects to UPS or additional battery pack
- Includes built-in 7A charger powered via hardwire 120VAC 30A input connection
- Internal DC disconnect
- 10 year design lifespan

Specifications

OVERVIEW	
UPC Code	037332185051
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Phase	3-Phase
BATTERY	
Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime
Expandable Runtime	Yes
DC System Voltage (VDC)	240
UPS Connection	15 ft. DC cable included
PHYSICAL	
External Battery Pack Form Factor	Tower
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	167.64 x 116.84 x 121.92
Shipping Dimensions (hwd / in.)	66.00 x 46.00 x 48.00
Shipping Weight (kg)	1,206.56
Shipping Weight (lbs.)	2660.00
Unit Dimensions (hwd / cm)	149.9 x 73.7 x 80
Unit Dimensions (hwd / in.)	59 x 29 x 31.5
Unit Weight (kg)	1,156.66
Unit Weight (lbs.)	2550
Unit Weight Details	Floor loading of 369 lbs per sq. ft. / 1804 kg per sq. meter
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>