

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	RELEASE TO PRODUCTION	22SEP2022	SS	JDB
	A2	DIMENSIONAL TOLERANCES REMOVED	28SEP2022	SS	JDB
	A3	NOTE 3 ADDED (PROP 65 WARNING)	07FEB2023	SS	JDB

D

C

B





A

D


C

B


A



CONTACT 6
CONTACT 3
CONTACT 2
CONTACT 1



RECOMMENDED STRIPPING LENGTHS



COLOR ALLOCATION OF TERMINAL
WIRE TO RJ45 CONTACT:


CONTACT NO.	WIRE COLOR
1	YELLOW
2	ORANGE
3	WHITE
6	BLUE

1 MATES WITH RJ45 SOCKET ACC. TO
IEC 60603-7:2008

2 VISUAL INSPECTION, OF THE DIE
CAST PARTS, ACCORDING TO
TE-SPEC. 101-85241

3 PROP 65 WARNING LABEL: SEE SHEET 2

50	10	1	CONNECTOR PACKED WITH INSTRUCTION SHEET
-3	-2	-1	DESCRIPTION
QTY REQD PER ASSY			PART LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SHARMA 15SEP2021	 TE Connectivity	
DIMENSIONS: mm		CHK N TAMMINEN 15SEP2021		
		APVD J DE BRUIJN 15SEP2021		
		PRODUCT SPEC 108-94864		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-94770	NAME RJ45 FIELD INSTALLABLE CABLE CONN. 90	
MATERIAL GD-Zn		WEIGHT -	SIZE A3	CAGE CODE 00779
FINISH Ni		CUSTOMER DRAWING	DRAWING NO C-2383217	RESTRICTED TO -
		SCALE 2:1	SHEET 1 OF 2	REV A3

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


NOTES: CONTINUATION FROM SHEET 1:

3 PROP 65 WARNING LABEL:

- THE WARNING LABEL ON THE PRODUCT OR LOWEST LEVEL PACKAGING.
- CHEMICAL NAME: ANTIMONY TRIOXIDE



WARNING: This product can expose you to chemicals including ANTIMONY TRIOXIDE which is known to the state of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SHARMA 15SEP2021	 TE Connectivity			
		CHK N TAMMINEN 15SEP2021				
DIMENSIONS: mm		APVD J DE BRUIJN 15SEP2021	NAME RJ45 FIELD INSTALLABLE CABLE CONN. 90			
		PRODUCT SPEC 108-94864	-			
		APPLICATION SPEC 114-94770				
MATERIAL GD-Zn	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 0.3 3 PLC ± 4 PLC ± ANGLES ±3° FINISH Ni	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2383217	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 2 OF 2	REV A3	