



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire.
Propriete de c FCI. Droits de reproduction FCI.

PRODUCT NUMBER
10034908-003
10034908-003LF












NOTE:
1. MATERIAL
   HOUSING: HIGH TEMPRATURE THERMOPLASTIC
   UL 94 V-0 FLAME RETARDANT, BLACK.
   TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
   PLATING: CONTACT AREA: 30u" Au OVER 50u" Ni UNDER ALL
   SOLDER TAIL: 100u" MATTE PURE TIN OVER 50u" Ni UNDER.
2. PRODUCT SPECIFICATION: GS-12-279.
3. PRODUCT PACKAGING SPEC: GS-14-937.
4. PART NUMBER 10034908-003LF MEETS EUROPEAN UNION
   DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED
   IN GS-22-008.
   THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
   TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDER APPLICATION
   WITH A CIRCUIT BOARD.
5. MANUFACTURER'S NAME, P/N AND DATE CODE
   TO APPEAR ON THIS SURFACE AS PER GS-24-007.






DETAIL A
SCALE 2:1



SECTION A-A
SCALE 3:2



mat'l code	-	tolerances unless otherwise specified			
		linear	0.X ±0.8		
			0.XX ±0.25		
			0.XXX ±0.13		
		angles	0° ±2°		
		dr	STEVEN WANG	11/10/05	
		engr	STEVEN WANG	11/10/05	
		chr	VICTOR LIN	11/10/05	
		appd	JOSEPH HSIA	11/10/05	

ltr	ecn no.	dr	date
A	DG05-0451	SW	03/15/06
B	DG06-0306	RYAN	08/21/06
C	DG06-0485	RYAN	11/21/06
D	DG06-0524	JULIA	12/26/06

sheet index	revision	D	D
	sheet	1	2

CUSTOMER
COPY
projection
MM
scale 1:1

FCI
www.fciconnect.com
title: SRADDLE MOUNT TYPE POWER EDGE CARD
product family: POWER EDGE CARD
code: 213
size: A
dwg no: 10034908-003
sheet: 1 of 2
cage code: 88516


All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

Pro/E
PDM: Rev:D
STATUS: Released
Printed: Dec 03, 2010


Downloaded from Arrow.com.

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du propietaire.
Propriete de c FCI. Droits de reproduction FCI.


PRODUCT NUMBER
10034908-003
10038908-003LF




RECOMMENDED PC BOARD LAYOUT
FOR CONNECTOR SOLDER TAILS




SECTION A-A





SEE DETAIL B



DETAIL B
SCALE 4:1

RECOMMENDED MATING BOARD EDGE CONFIGURATION

ltr	ecn no.	dr	date
D			

mat'l code	-

tolerances unless otherwise specified		
linear	0.X ±0.8	
	0.XX ±0.25	
	0.XXX ±0.13	
angles	0° ±2°	
dr	STEVEN WANG	11/10/05
engr	STEVEN WANG	11/10/05
chr	VICTOR LIN	11/10/05
appd	JOSEPH HSIA	11/10/05

CUSTOMER
COPY
projection
MM
scale 1:1

www.fciconnect.com

title STRADDLE MOUNT TYPE POWER EDGE CARD

product family	POWER EDGE CARD	code 213
size A	dwg no 10034908-003	sheet 2 of 2

sheet index	revision sheet

cage code 22526

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

Downloaded from Arrow.com.