THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
H	—

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	EHC0-0319-04	03AUG04	KNK	BM
	B	ECR-10-018652	10SEP10	JS	MQW

CONNECTOR ASSEMBLY

EXEMPLARY LOADED




CONTACT DIMENSIONS




RECOMMENDED PCB-HOLE LAY-OUT

COMPONENT SIDE SHOWN



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

CONTACT LAYOUT



NOTES:

1. MATERIAL HOUSING : GREY GLASSFILLED POLYESTER UL-RATING V∅
   CONTACT : PHOSPHORBRONZE
2. CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.
3. CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
4. PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.

-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	1,3	0,8	0,5	1-5352961-1 (2)
-	-	-	1,3	0,8	0,5	5352961-1
- - -	- - -	- - -	CONTACT UNDER-COATING [µm Ni MIN.]	CONTACT AREA [µm Au MIN.]	ACTION-PIN AREA [µm Sn MIN.]	PART NUMBER
	CONTACT FINISH					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
±0.2

MATERIAL -

FINISH -

DWN	K.N.KIRAN	25AUG2004
CHK	B.MOOIJ	22MAR2005
APVD	B.MOOIJ	22MAR2005
PRODUCT SPEC	108-19082	
APPLICATION SPEC	114-19029	
WEIGHT	-	

Tyco Electronics Corporation
's-Hertogenbosch,5222AR-32

NAME
Z-PACK 2mm HM TYPE C
55 POS. RIGHT ANGLE MALE
CONNECTOR ASSEMBLY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-5352961	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV B

5352961

AMP 1471-9 REV 31MAR2000

Downloaded from Arrow.com.

..\..\AutoCAD_PROJECTS\ENGG_SERVICE(CONNECTOR HOLLAND)\EHC0-0319-04\CORRECTED-customer\24-03-05\5352961.c_A.dwg