

Terminals & Splices > Power Terminals

214783-E

ACTIVE

Power Terminals, Power Tap, Terminates To Printed Circuit Board, 10 Position, 2.54 mm [.1 in] Centerline, Power, Solid, Tin (Sn), Copper Alloy



TE Internal #: **214783-E**
TE Internal Description: **EPSVA KS GD-8 TL 10 3,8 SN * STROMVERSOR**

Power Terminal Type : **Power Tap**
Product Terminates To : **Printed Circuit Board**
Number of Positions : **10**
Contact Current Rating (Max) (A): **40**
Centerline (Pitch) : **2.54 mm [.1 in]**

Add to List | [Similar Products](#) | Digital Datasheet



Compatible Parts & Tooling

DocumentsFeaturesProduct Compliance

Product Drawings

EPSVA KS GD-8 TL 10 3,8 SN * STROMVERSOR
 EPSVA KS GD-8 TL 10 3,8 SN * STROMVERSOR
English

CAD Files

3D PDF
 3D_CVM_CVM_214783-E_1.pdf
3D
Customer View Model
 ENG_CVM_CVM_214783-E_1.3d_igs.zip
English
 ENG_CVM_CVM_214783-E_1.3d_stp.zip
English
 ENG_CVM_CVM_214783-E_1.2d_dxf.zip
English

Datasheets & Catalog Pages

ERNI Power Taps
 GER_DS_erni-power-taps-ds_2209.pdf
German
 ENG_DS_erni-power-taps-ds_2209.pdf
English

SHOP OUR DISTRIBUTORS

North America

See all price breaks

Distributor	1	10,000	Buy
Arrow Electronics Inc. 6,493 in-stock	\$2.948	\$1.854	SHOP NOW

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Compatible Parts

Filter By Specification

214779-E
Power Terminals, Power Tap, Terminates To Printed Circuit...
From: \$2.610
In-Stock
[VIEW PRODUCT](#)

214780-E
Power Terminals, Power Tap, Terminates To Printed Circuit...
From: \$3.076
In-Stock
[VIEW PRODUCT](#)

214781-E
Power Terminals, Power Tap, Terminates To Printed Circuit...
From: \$1.322
In-Stock
[VIEW PRODUCT](#)

214784-E
Power Terminals, Power Tap, Terminates To Printed Circuit...
In-Stock
[VIEW PRODUCT](#)

214785-E
Power Terminals, Power Tap, Terminates To Printed Circuit...
In-Stock
[VIEW PRODUCT](#)

214786-E
Power Terminals, Power Tap, Terminates To Printed Circuit...
From: \$2.857
In-Stock
[VIEW PRODUCT](#)

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

POWER TERMINALS

214783-E
Power Terminals, Power Tap, Terminates To Printed Circuit...

In-Stock

Power Terminal Type : **Power Tap**
Product Terminates To : **Printed Circuit Board**
Number of Positions : **10**
Contact Current Rating (Max) : **40 A**
Centerline (Pitch) : **2.54 mm**

Customers Also Bought

W2S
Automotive Connector Locks & Position Assurance...
\$0.094 per unit
Inventory: In-Stock
[Add To Cart](#)

W2P
Automotive Connector Locks & Position Assurance...
\$0.106 per unit
Inventory: In-Stock
[Add To Cart](#)

282104-1
Housing for Male Terminals, Wire-to-Board /...
\$0.909 per unit
Inventory: In-Stock
[Add To Cart](#)

282080-1
Housing for Female Terminals, Wire-to-Wire /...
\$0.981 per unit
Inventory: In-Stock
[Add To Cart](#)

Contact Our Team – 24/7 Support

+1 800 522 6752
 Live Chat
See Support Details

Connect With Us

Access Partner Information

Distributors
Suppliers
TE Notice on COVID

Get Answers Now

Authorized Distributors & Resellers
Product FAQs
Samples FAQs
TE Store FAQs
Terms and Conditions of Sale
Samples Terms and Conditions

Select Country

United States (EN)
Germany (DE)
China (中文)
Japan (日本語)
See All Countries