SC-JB8-2-OR

TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → Short Circuit Bridges

General Information

Extended Product Type:	SC-JB8-2-OR
Product ID:	1SNK900656R0000
EAN:	3472599857575
Catalog Description:	SC-JB8-2 Short circuit bridges - Orange
Long Description:	- Allow safe short-circuiting of Current Tranformers circuits, - Insulated, - F ully operated by screwdriver, - Short circuited fixed position secured thanks to AJS9 tightening, - Adapted hook shape maintains the bridge on the term inal block in the non short-circuited position, - The orange version can be u sed as fixed jumpers.

Ordering

Color:	Orange
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85389099

Popular Downloads

Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	8 mm
Product Net Height:	24.6 mm
Product Net Depth / Length:	13.9 mm
Product Net Weight:	2 g

Technical

Spacing:	8 mm
Function:	Short Circuit Bridges
Rated Current (I_n):	Main Circuit 5 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	D6/8.ST.RS ZS10-PE-R1 ZS10-R1 ZS10-ST ZS10-ST-T4

Downloaded from Arrow.com.

Technical UL/CSA

Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230528F0200

Classifications

Object Classification Code:	X

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	125 mm
Package Level 1 Depth / Length:	170 mm
Package Level 1 Height:	20 mm
Package Level 1 Gross Weight:	0.05 kg
Package Level 1 EAN:	3472599857575
Package Level 2 Units:	500 piece
Package Level 2 Width:	175 mm
Package Level 2 Depth / Length:	227 mm
Package Level 2 Height:	130 mm
Package Level 3 Units:	24000 piece
Product Packing Type:	Bag



Downloaded from Arrow.com.