



Part Number : [1300970163](#)

Product Description : Deluxe Cord Grips Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437")

Series Number : 130097

Status : Active

Product Category : Cable Grips

Engineering Part Number : 36254



Documents and Resources

Drawings

[1300970163 sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant with Exemption 6(b)-II per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|---------------------|--|
| Status | Active |
| Category | Cable Grips |
| Series | 130097 |
| Description | Deluxe Cord Grips Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437") |
| Hazardous Locations | Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2 |
| NEMA Rating | NEMA 4 |
| Product Name | Deluxe Cord |
| Type | Strain Relief Grip |
| UPC | 78678836254 |

Agency

| | |
|-----|---------|
| CSA | LR32159 |
| UL | E76954 |

Physical

| | |
|----------------------------|---------------------------|
| Approximate Break Strength | N/A |
| Bale Length | 0.079m (3.13") |
| Body Style | Straight |
| Cable Diameter | 9.53-11.10mm (.375-.437") |
| Color - Grommet | Black |
| Eye Type | N/A |
| Gender | Male |
| Material - Body | Aluminum |
| Material - Grip | Stainless Steel |
| Mesh Length | 0.159m (6.25") |

| | |
|-----------------|----------|
| Number of Holes | N/A |
| O-Ring | N/A |
| Thread Size | 1/2" NPT |

Mates With / Use With

Use with Part(s)

| Description | Part Number |
|---|-------------------|
| MAX-LOC Lock Nut 1/2" NPT | <u>1300990143</u> |
| MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black | <u>1300990149</u> |
| MAX-LOC O-Ring, 1/2" NPT | <u>1301800314</u> |

This document was generated on May 20, 2026