

# KSS 5 - Short-circuit connector



2303543

<https://www.phoenixcontact.com/ae/products/2303543>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Short-circuit connector, pitch: 5 mm, number of positions: 2, color: black



## Commercial data

Item number	2303543
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE1
Product key	BE1Z3X
GTIN	4017918058517
Weight per piece (including packing)	3.69 g
Weight per piece (excluding packing)	3.66 g
Customs tariff number	85366990
Country of origin	PL

# KSS 5 - Short-circuit connector



2303543

<https://www.phoenixcontact.com/ae/products/2303543>

## Technical data

### Product properties

Product type	Short-circuit connector
Number of positions	2
Pitch	5 mm

### Dimensions

Pitch	5 mm
-------	------

### Material specifications

Color	black (RAL 9005)
Material	Copper
Flammability rating according to UL 94	V2
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# KSS 5 - Short-circuit connector



2303543

<https://www.phoenixcontact.com/ae/products/2303543>

## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 9.0	EC000489
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# KSS 5 - Short-circuit connector



2303543

<https://www.phoenixcontact.com/ae/products/2303543>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Middle East FZ LLC  
1201N-1206N, Dubai Science Park Towers – North  
P.O. Box 345002, Dubai, United Arab Emirates  
(+971) 4 437-0324  
[info-me@phoenixcontact.com](mailto:info-me@phoenixcontact.com)