



Part Number : [444412003](#)

Product Description : 7.50mm Pitch Sabre
Receptacle Crimp Housing, UL 94V-0, 3 Circuits, Black

Series Number : 44441

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[444412003_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[PK-44441-001-001.pdf](#)

[PS-44441-9999-001.pdf](#)

[444410000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	44441
Description	7.50mm Pitch Sabre Receptacle Crimp Housing, UL 94V-0, 3 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Positive mating lock and integrated Terminal Position Assurance (TPA) standard.
Product Name	Sabre
UPC	800754366793

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No

Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.725/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +75°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-0, 3 Circuits, Black, Black	436802003
Sabre Headers	43160
Sabre Right-Angle Headers	46007

Use with Part(s)

Description	Part Number
Sabre Female Crimp Terminals	43375

This document was generated on Jan 23, 2026