

Bazaar / Wireless / RF&FM / 433MHz wireless ISM transceiver module



433MHz wireless ISM transceiver module

SKU 317010003

WT -4432G are highly integrated wireless ISM transceiver module

IN STOCK 2 Available

Qty:

- 1 +

ADD TO CART

Description

WT -4432G are highly integrated wireless ISM transceiver module. Very low receive sensitivity (-121dBm/1200bps), coupled with industry leading +20dBm output power ensures extended range and improved link performance. Built-in antenna diversity and support for frequency hopping can be used to further extend range and enhance performance.

Features

- Frequency Range: 433 MHz
(other frequencies need to be customized)
- Sensitivity = -121 dBm at 1200bps
- Max output power:20dBm
- 85mA@+20dBm transmit
- Data Rate = 0.123 to 256 kbps
- FSK,GFSpplly = 1.8 to 3.6 V
- Ultra low pK and OOK modulation
- Power Suower shutdown mode
- Digital RSSI
- Wake-up timer
- Auto-frequency calibration (AFC)

See More

Questions and Answers

Have a question about this? Ask people who own it.



View History

Downloaded from [Arrow.com](#)

Documents

[Datasheet](#)

Recommendations



433Mhz Wireless Serial Transceiver...



433Mhz RF Module WT-4432G - ISM...



Seeeduino Stalker v3



Linkit Smart 7688 Duo



ESP-32S Wifi Bluetooth Combo Module



Doppler X band Radar detector sensor...



Mini PIR Motion Sensor Module



433MHz 4-Button Car Key Fob



433&868&915MHz Ultra low...



SeeedStudio BeagleBone Green Wireless



315Mhz RF link kit



Temperature sensor with steel head

BACKORDER



Piezo Sensor - MiniSense 100

ADD TO CART



Photo interrupter (OS25B10)

ADD TO CART




G1&2" Water Flow Sensor

ADD TO CART



Piezo Vibration Sensor

ADD TO CART



Grove - Moisture Sensor



KiwiSDR Board



0-14mm hole saw



Bus Pirate v3.6 universal serial...



1W Solar Panel 80X100



Small Size and High Torque Stepper...



MDBT42Q - nRF52832 based BLE module



RESK - Resistor Kit

Wireless Charging Module - 5V&1A

POPULAR SEARCHES

- PCB Manufacturing
- PCB Stencil
- Arduino
- XBee
- Arduino Shield
- Beaglebone Black
- Raspberry Pi
- Raspberry Pi Touchscreen
- LinkIt
- Cubieboard
- Beaglebone Cape
- FPGA
- LinkIt ONE
- Crazyflie 2.0
- Raspberry Pi 3 Model B
- RF Explorer
- DSO Nano v3
- MediaTek X20
- HiKey Board
- rplidar
- raspberry pi relay
- RPLIDAR A2

 SHIPPING INFORMATION

 KNOWLEDGE BASE

 HELP CENTER

Seed Info

Reach Us

Distributors

Designers

Careers

Site Map

Customer Service

Contact Us

Customer Support

Technical Support

Terms and Conditions

Order Information

Shipping Information

Payment Information

Warranty and Return

Terms of use

Stay Tuned

Subscribe to get the latest product releases, activities and tutorials from Seed Studio.





