



Color: ■ orange

| Physical data |  |                       |
|---------------|--|-----------------------|
| Width         |  | 2.5 mm / 0.098 inches |
| Height        |  | 113 mm / 4.449 inches |
| Depth         |  | 50 mm / 1.969 inches  |

| Material data                      |  |                                                                          |
|------------------------------------|--|--------------------------------------------------------------------------|
| Note (material data)               |  | <a href="#">Information on material specifications can be found here</a> |
| Color                              |  | orange                                                                   |
| Material group                     |  | I                                                                        |
| Insulation material (main housing) |  | Polyamide (PA66)                                                         |
| Flammability class per UL94        |  | V0                                                                       |
| Fire load                          |  | 0.16 MJ                                                                  |
| Weight                             |  | 5.9 g                                                                    |

| Environmental requirements       |  |                 |
|----------------------------------|--|-----------------|
| Processing temperature           |  | -35 ... +85 °C  |
| Continuous operating temperature |  | -60 ... +105 °C |

| Commercial data       |  |                                  |
|-----------------------|--|----------------------------------|
| Product Group         |  | 1 (Rail Mounted Terminal Blocks) |
| PU (SPU)              |  | 50 (25) pcs                      |
| Packaging type        |  | Box                              |
| Country of origin     |  | DE                               |
| GTIN                  |  | 4017332150170                    |
| Customs tariff number |  | 85389099990                      |



| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121702             |
| eCl@ss 10.0            | 27-14-11-33          |
| eCl@ss 9.0             | 27-14-11-33          |
| ETIM 9.0               | EC000886             |
| ETIM 10.0              | EC000886             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 280-306

↓

| Documentation |            |                 |   |
|---------------|------------|-----------------|---|
| Bid Text      |            |                 |   |
| 280-306       | 19.02.2019 | xml<br>2.51 KB  | ↓ |
| 280-306       | 28.04.2017 | doc<br>22.50 KB | ↓ |

| CAD/CAE-Data         |                           |
|----------------------|---------------------------|
| CAD data             | CAE data                  |
| 2D/3D Models 280-306 | EPLAN Data Portal 280-306 |
|                      | WSCAD Universe 280-306    |
|                      | ZUKEN Portal 280-306      |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)