
Toroidal Coil Inductor



ATCA-01

Request Samples Check Inventory

18.0 x 11.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Low EMI/RFI toroid topology
- High saturation currents up to 3A
- High efficiency powered iron core
- Wide operating temperature range -40°C to 105°C
- Vertical and horizontal orientations optimize EMI/RFI
- Compatible with low cost through-hole assembly

Applications

- High power switch-mode power supplies
- High power LED ballasts
- Power line filters
- High power audio filters
- Solar inverters
- White goods
- Motor drivers

Electrical Specifications

Part Number	L(µH)	Tolerance	DCR(Ω)	IDC(A)	Dimension (mm) E (dia.)
		(%)	(max)	(max)	(Nom)
ATCA-01-200M	20	M	0.021	3.0	0.70
ATCA-01-300M	30	M	0.035	2.0	0.60
ATCA-01-600M	60	M	0.038	3.0	0.70
ATCA-01-680M	68	M	0.101	1.0	0.45
ATCA-01-101M	100	M	0.081	2.0	0.60
ATCA-01-221M	220	M	0.190	1.0	0.45

Test Conditions

Test Freq for L: 1KHz, 0.1Vrms

I_{DC}: max. 10% inductance drop from initial value

Operating Temperature: -40˚C ~ +105˚C (including self-temperature rise)
Power Rating: 10W Max
Storage Condition: -20˚C ~ +40˚C
ATCA-01 is RoHS/RoHSII Compliant and Pb free

ABRACON


5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION B : 10/22/2024

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.

Toroidal Coil Inductor



ATCA-01

Request Samples | Check Inventory


18.0 x 11.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

Part Identification


ATCA-01- ☐☐ - ☐

Inductance Code	Tolerance	Packaging
See Electrical Specification table	M = ± 20%	H: Horizontal V: Vertical

Mechanical Specifications



Vertical



Horizontal

Series	A	B	C	D	F
ATCA-01	18.0 Max	11.5 Max	11.0 Max	17.5 Max	15.0 Max

Dimensions: mm

ABRACON


5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION B : 10/22/2024

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.

Toroidal Coil Inductor



ATCA-01

Request Samples Check Inventory

18.0 x 11.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

Materials

Part Number	Material	UL
Core	Iron Powder	NA
Wire	155℃	E194410
Soldering	Sn-Cu	

Packaging

Part Number	Pcs / Tray	Trays / Carton	Pcs / Carton
ATCA-01-xxxM-V	150	6	900
ATCA-01-xxxM-H	150	6	900

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.

ABRACON

5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION B : 10/22/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Downloaded from Arrow.com.