



2310

20 Amp, 125 Volt, Flush Mount Locking Receptacle, Industrial Grade

20 Amp, 125 Volt, NEMA L5-20R, 2P, 3W, Flush Mtg Locking Receptacle, Industrial Grade, Grounding, V-0-MAX - BLACK

ROHS Compliant : Yes

Leviton's Industrial Grade Locking Devices are built to provide unparalleled quality and superior performance in the most severe industrial settings. Leviton combines the best materials available with superior production standards to produce a broad selection of Locking Devices of unmatched flexibility and dependability.

- Ideal for motor loads, such as shop vacs and pool pumps, and generators

UPC Code : 078477801109

Country Of Origin : Please Contact Customer Service

NEMA :  L5-20R

Technical Information

Electrical Specifications

Amperage : 20 A

Current Limiting : Full Rated Current

Dielectric Voltage : Withstands 2000V per UL498

Grounding : Grounding

Pole : 2

Temperature Rise : Max 30C after 250 cycles OL at 200 percent rated current

Voltage : 125 VAC

Wire : 3

Material Specifications

Base Material : Valox|Valox

Body Material : Nylon

Color : Black

Cover Material : Valox 357

Face Material : Ultramid|Ultramid

Ground Clips : Nickel-Plated Brass

Ground Contacts : Brass

Grounding Screw : Chromated Brass

Line Contacts : Brass

Environmental Specifications

Flammability : Rated V-0 per UL 94

Operating Temperature : -40° C to 60°C

Mechanical Specifications

Cord Range : 0.385 to 0.780

Product ID : Ratings and NEMA I.D. permanently marked on device

Screw Terminal Torque : 14-18 in-lbs

Terminal Accom. : 14-8 AWG

Terminal ID : Marked on Device

Termination : Back & Side

Torque Range : 14-16 in-lbs

Strap Material : Nickel-Plated
Brass

Terminal Clamps : Zinc-Plated
Brass

Terminal Screws : Chromated
Brass

Product Features

Base Material : Valox|Valox

Color : Black

Face Material :
Ultramid|Ultramid

NEMA : L5-20R

Warranty : Limited Lifetime
Warranty|Limited Lifetime
Warranty

Standards and Certifications

ANSI : C-73

CSA : C22.2 No. 42

NEMA : WD-1 & WD-6

NOM : 057

UL : 498

UL Fed Spec : W-C-596


UL Fed Spec WC-596 : File
E13399

UL498 : File E13399

Warranty

Warranty : Limited Lifetime
Warranty|Limited Lifetime
Warranty

Wiring Diagram



SPECIFICATION SUBMITTAL

JOB NAME:

JOB NUMBER:

CATALOG NUMBERS:

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.
T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-461-2002 ·
FAX: +1-800-824-3005 ·

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)
5386- 1797 ·

Visit our Website at: www.leviton.com

© 2026 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without
notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/company/about-leviton/locations

© 2026 Leviton Manufacturing Co., Inc.