



Part Number : [347910021](#)

Product Description : Mini50 Unsealed Receptacle, Single Row, Bridged, 2 Circuits, Polarization Option B, Gray

Series Number : 34791

Status : Active

Product Category : Connector Housings

Documents & Resources

Drawings

[Drawing 347910021_sd.pdf](#)

[Packaging Design Drawing PK-31301-538-001.pdf](#)

[Packaging Design Drawing PK-31301-538-001.pdf](#)

3D Models and Design Files

[3D Model 347910021_stp.zip](#)


Specifications

[Application Specification AS-34791-020-CH-001.pdf](#)

[Test Summary 347910020-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	34791
Description	Mini50 Unsealed Receptacle, Single Row, Bridged, 2 Circuits, Polarization Option B, Gray
Application	Automotive, Power, Wire-to-Board
Product Family	Mini50 Connection Systems
Product Name	Mini50
UPC	889056527545

Physical

Circuits (maximum)	2
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	0.540/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	B
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Inline Housing, Single Row, 2 Circuits, Polarization B, Light Gray	<u>2037000021</u>
Mini50 Unsealed Single Row Right-Angle Headers	<u>34912</u>
Mini50 Unsealed Single Row Inline Housings	<u>203700</u>

Use with Part(s)

Description	Part Number
CTX50 Unsealed Receptacle Terminals	<u>560023</u>

This document was generated on Jul 29, 2024