

# D-QTTCB 1,5 - End cover

3205187

<https://www.phoenixcontact.com/us/products/3205187>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 49.9 mm, width: 2.2 mm, height: 99.6 mm, color: gray



## Commercial data

Item number	3205187
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE39
Product key	BE3Z1X
Catalog page	Page 258 (C-1-2019)
GTIN	4017918932572
Weight per piece (including packing)	4.916 g
Weight per piece (excluding packing)	4.727 g
Customs tariff number	85389099
Country of origin	DE

# D-QTTCB 1,5 - End cover

3205187

<https://www.phoenixcontact.com/us/products/3205187>



## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ( )
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

### Dimensions

Width	2.2 mm
Height	99.6 mm
Depth	49.9 mm

# D-QTTCB 1,5 - End cover



3205187

<https://www.phoenixcontact.com/us/products/3205187>

## Classifications

### ECLASS

ECLASS-13.0	27250301
-------------	----------

### ETIM

ETIM 9.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# D-QTTCB 1,5 - End cover

3205187

<https://www.phoenixcontact.com/us/products/3205187>



## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)