
Specification Sheet

Part Number: MB3A0A2H4



For use with HellermannTyton T18 - T30 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The acrylic-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 0.6 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.

Acrylic Adhesive Cable Tie Mount, 0.75 x 0.75", Use With T18-T30 Cable Tie, PA66, Black, 500/pkg

Article Number	151-28709
Type	MB3A
Color	Black (BK)
Quantity Per	pack
Product Description	MB3A adhesive mounts are for use with HellermannTyton T18 - T30 Series cable ties to provide stability when securing bundles. The acrylic adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.

Downloaded from Arrow.com.

Short Description	Acrylic Adhesive Cable Tie Mount, 0.75 x 0.75", Use With T18-T30 Cable Tie, PA66, Black, 500/pkg
Global Part Name	MB3A-PA66-BK
Length L (Imperial)	0.75
Length L (Metric)	19.0
Fixation Method	Adhesive
Width W (Imperial)	0.75
Width W (Metric)	19.0
Cable Ties	T18 - T30
Height H (Imperial)	.19
Height H (Metric)	4.8
Cable Tie Width Max (Imperial)	0.14
Cable Tie Width Max (Metric)	3.6
Mounting Hole Diameter D (Imperial)	0.12 "
Mounting Hole Diameter D (Metric)	3.0 mm
Mounting Hole Centers (Imperial)	0.52

Downloaded from Arrow.com.

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Acrylate with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-31°F to +158°F (-35 °C to +70 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
BABA Compliant	YES
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

Downloaded from Arrow.com.

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.