

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638112400

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for 1.50mm MX150 Blade Male Terminals, 14-16 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

Prototype and field repair. Type: 4A

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Hand Crimp Tool

756054649671

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

428.885/zg

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381124HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin Plating, 14 AWG, Right Reel Payoff	330000001
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin Plating, 16, 18 and 20 AWG, Right Reel Payoff	330000002
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin	330001001

Plating, 14 AWG, Left Reel Payoff MX150 Male	<u>330001002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Tin Plating, 16, 18 and 20 AWG, Left Reel Payoff MX150 Male	<u>330110002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Gold Plating, 14 AWG, Left Reel Payoff MX150 Male	<u>330110004</u>
Terminal for Mat- Sealed or Unsealed Connectors, Gold Plating, 16, 18 and 20 AWG, Left Reel Payoff MX150 Male	<u>330111002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Gold Plating, 14 AWG, Right Reel Payoff MX150 Male	<u>330111004</u>
Terminal for Mat- Sealed or Unsealed Connectors, Gold Plating, 16, 18 and 20 AWG, Right Reel Payoff MX150 Male	<u>330112002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 16, 18 and 20 AWG, Right Reel Payoff MX150 Male	<u>330112003</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 14 AWG, Right Reel Payoff MX150 Male	<u>330113002</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 16, 18 and 20 AWG, Left Reel Payoff MX150 Male	<u>330113003</u>
Terminal for Mat- Sealed or Unsealed Connectors, Silver Plating, 14 AWG, Left Reel Payoff	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION