

PS-5 - Test plug

3030983

<https://www.phoenixcontact.com/us/products/3030983>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, Modular test plug, number of positions: 1, color: red

Your advantages

- The test plugs make contact in the function shaft of terminal blocks from the CLIPLINE complete system
- Test adapters can be assembled individually using PS-... modular test plugs

Commercial data

Item number	3030983
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4017918818920
Weight per piece (including packing)	3.4 g
Weight per piece (excluding packing)	1.2 g
Customs tariff number	85366990
Country of origin	PL

PS-5 - Test plug

3030983

<https://www.phoenixcontact.com/us/products/3030983>



Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1


Electrical properties

Maximum load current	2 A
Max. voltage	250 V

Connection data

Maximum load current	2 A
Connection method	Spring-cage connection
Conductor cross section flexible	0.14 mm ² ... 1 mm ²
Conductor cross section rigid	0.14 mm ² ... 1 mm ²
Cross section AWG	26 ... 18

Dimensions

Dimensional drawing	
Width	5.2 mm
Height	22.4 mm
Depth	60 mm

Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %


PS-5 - Test plug

3030983

<https://www.phoenixcontact.com/us/products/3030983>



Drawings



PS-5 - Test plug

3030983

<https://www.phoenixcontact.com/us/products/3030983>



Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-13.0	27250304

ETIM

ETIM 9.0	EC002555
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PS-5 - Test plug

3030983

<https://www.phoenixcontact.com/us/products/3030983>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com