

**Part Number :** [2207183001](#)

**Product Description :** HyperQube 6.00mm, Plug Housing, Blue, Bag

**Series Number :** 220718

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[2207183001\\_sd.pdf](#)

[2207181001-PK-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[2207170001-AS-000.pdf](#)

[2207170001-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	220718
Description	HyperQube 6.00mm, Plug Housing, Blue, Bag
Application	Power, Wire-to-Board, Wire-to-Busbar
Product Name	HyperQube
UPC	196823234101

### Agency

UL	E29179
----	--------

### Physical

Circuits (maximum)	1
Color - Resin	Blue
Diameter	6.00mm
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	No

Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.786/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Temperature Range - Operating	-40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
HyperQube 6.00mm, Screw Mount, Right-Angle PCB Receptacle, Blue, Tray	<u><a href="#">2207173001</a></u>

### Use with Part(s)

Description	Part Number
HyperQube 6.00mm Copper Alloy Male Crimp Contact, 2 AWG, Bag	<u><a href="#">2207191001</a></u>
HyperQube 6.00mm Copper Alloy Male Crimp Contact, 4 AWG, Bag	<u><a href="#">2207191002</a></u>
HyperQube 6.00mm Copper Alloy Male Crimp Contact, 6 AWG, Bag	<u><a href="#">2207191003</a></u>

---

This document was generated on Apr 29, 2026