

[\(/en\)](#)

Search



AMD EPYC™ 7351P

[**SPECIFICATIONS**](#)[**DRIVERS & SUPPORT \(/EN/SUPPORT/CPU/AMD-EPYC/AMD-EPYC-7001-SERIES/AMD-EPYC-7351P\)**](#)**AMD EPYC™ 7351P**[Share this page](#)

AMD EPYC™ 7351P

Specifications

of CPU Cores: 16**# of Threads:** 32**Base Clock:** 2.4GHz**Max Boost Clock:** Up to 2.9GHz**All Core Boost Speed:** 2.9GHz**Total L3 Cache:** 64MB**Package:** SP3**Socket Count:** 1P

PCI Express® Version: PCIe 3.0 x128

Default TDP / TDP: 155/170W

System Memory

System Memory Specification: 2400MHz/2666MHz

System Memory Type: DDR4

Memory Channels: 8

Per Socket Mem BW: 153.6 GB/s/170.6 GB/s

Key Features

Workload Affinity

General Purpose
GPU/FPGA Accelerated
Storage

Foundation

Product Family: AMD EPYC™

Product Line: AMD EPYC™ 7001 Series

Platform: Server

OPN Tray: PS735PBEVGPAF

OPN PIB: PS735PBEAFWOF

Related Products

AMD EPYC™ 7601 (/en/products/cpu/amd-epyc-7601)

of CPU Cores: 32

of Threads: 64

Max Boost Clock: Up to 3.2GHz

Base Clock: 2.2GHz

Default TDP / TDP: 180W

[LEARN MORE \(/EN/PRODUCTS/CPU/AMD-EPYC-7601\)](/EN/PRODUCTS/CPU/AMD-EPYC-7601)

AMD EPYC™ 7551P (/en/products/cpu/amd-epyc-7551p)

of CPU Cores: 32

of Threads: 64

Max Boost Clock: Up to 3.0GHz

Base Clock: 2.0GHz

Default TDP / TDP: 180W

[LEARN MORE \(/EN/PRODUCTS/CPU/AMD-EPYC-7551P\)](/EN/PRODUCTS/CPU/AMD-EPYC-7551P)

AMD EPYC™ 7551 (/en/products/cpu/amd-epyc-7551)

of CPU Cores: 32

of Threads: 64

Max Boost Clock: Up to 3.0GHz

Base Clock: 2.0GHz

Default TDP / TDP: 180W

[LEARN MORE \(/EN/PRODUCTS/CPU/AMD-EPYC-7551\)](/en/products/cpu/amd-epyc-7551)

[LOAD MORE \(?PAGE=1\)](?PAGE=1)

[Our Company \(/en/corporate/about-amd\)](/en/corporate/about-amd)

[Newsroom \(/en/corporate/newsroom\)](/en/corporate/newsroom)

[Careers \(/en/corporate/careers\)](/en/corporate/careers)

[Investors \(http://ir.amd.com\)](http://ir.amd.com)

[Contact Us \(/en/corporate/contact\)](/en/corporate/contact)



©2020 Advanced Micro Devices, Inc

[Terms and Conditions \(/en/corporate/copyright\)](/en/corporate/copyright)

[Privacy \(/en/corporate/privacy\)](/en/corporate/privacy)

[Cookie Policy \(/en/corporate/cookies\)](/en/corporate/cookies)

[Trademarks \(/en/corporate/trademarks\)](/en/corporate/trademarks)

[Statement on Forced Labor \(https://www.amd.com/system/files/documents/statement-human-trafficking-forced-labor.pdf\)](https://www.amd.com/system/files/documents/statement-human-trafficking-forced-labor.pdf)

[Fair and Open Competition \(/en/corporate/competition\)](/en/corporate/competition)

[UK Tax Strategy \(https://www.amd.com/system/files/documents/amd-uk-tax-strategy.pdf\)](https://www.amd.com/system/files/documents/amd-uk-tax-strategy.pdf)