

Home → Shop Tools → Measuring Tools → MaxiFlex Folding Ruler Combination Metric/Inch

# MaxiFlex Folding Ruler Combination Metric/Inch

Sale



Zoom

Be the first to review this product

MaxiFlex Folding Ruler Combination Metric & Inch

**SKU:** 61662

Add to Cart

Qty:

1



Add to Wishlist



Share on Facebook



Tweet This



Pin it

We accept

amazon pay

## Details

Molded with 30% Fiberglass Material  
Chemical, Water & Scratch Resistant  
Impact Resistant Tough Yet Flexible  
Play free Precision Joints & 90° stops

## Additional Info

SKU

61662

Weight (lbs)

0.3100

Maintenance Free, Won't Rust or Kink  
Deep embossed scale on both sides  
Metric Rulers Marked red at 10cm  
Inch Rulers Marked Red at 16" Intervals  
2 Meter / 78"  
Outside Reading Inch  
Inside Reading Metric  
5/8 wide, 10 Sections  
Deep Embossed  
1/16 & 16" Centers

Country of  
Manufacture

Switzerland

## WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

## Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

## You may also be interested in the following product(s)



Insulated 80 Piece Set In Rolling  
Tool Case

## Customers Also Bought



Wiha Hat

**Wiha Professional Quality  
Hand Tools**

**Wiha Tools USA Since 1985**

Wiha Activities In the USA Started in August of  
1985 bringing Wiha quality to professional tool

**Wiha Tools USA  
Willi Hahn Corporation**

A Subsidiary of [Wiha Werkzeuge GmbH](#)



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

**We accept**

[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm  
CST USA**

1348 Dundas Cir,  
Monticello, MN 55362  
Customer Service Email:  
[cservice@wihatools.com](mailto:cservice@wihatools.com)  
Tel: 763-295-6591  
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools  
In Stock**



**Newsletter**

[Subscribe](#)

© 2017 Wiha Tools USA. All Rights Reserved.

**SHIPS FREE**

