



Plug









Wire Terminated




Solder Cup


Socket







Wire Terminated



Solder Cup

NO. OF CONTACTS	A ± .010"	B MAX. (Plug) Min. (Socket)	C +.010" -.018"	D ±.005"	E ± .010"	F Max.
9 Plug	.778	.2918	.398	.565	.208	.173
9 Socket	.778	.2922	.398	.565	.208	.173
15 Plug	.928	.4418	.548	.715	.208	.173
15 Socket	.928	.4422	.548	.715	.208	.173
21 Plug	1.078	.5918	.698	.865	.208	.173
21 Socket	1.078	.5922	.698	.865	.208	.173
25 Plug	1.178	.6918	.798	.965	.208	.173
25 Socket	1.178	.6922	.798	.965	.208	.173
31 Plug	1.328	.8418	.948	1.115	.208	.173
31 Socket	1.328	.8422	.948	1.115	.208	.173
37 Plug	1.478	.9918	1.098	1.265	.208	.173
37 Socket	1.478	.9922	1.098	1.265	.208	.173
51 Plug	1.428	.9418	1.048	1.215	.250	.220
51 Socket	1.428	.9422	1.048	1.215	.250	.220

DRAWING REVISIONS
(RELEASE DATE ON FILE)

REV	DOCUMENT	APP	APPROVAL DATE
1	CCSXXXXX	JW	ON FILE

MODELED BY:

UNITS
ENGLISH INCHES

PRO/E

CINCH
1700 FINLEY RD
LOMBARD, IL. 60148

CATALOG DRAWING

UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS ARE IN INCHES

DESIGN ENGINEER: J. WARRAICH
DATE: 3/14/22

TITLE: DURA-CON ALL PLASTIC MICRO-D, SOLDER CUP AND WIRE TERMINATED


MATERIAL
CONTROL SPEC NUMBER
MATERIAL SPEC NUMBER
FINISH
PROJECT NUMBER

APPROVALS
ON FILE


CAD FILE NUMBER: M83513
DRAWING NUMBER: M83513
CAGE IDENT NO.: 71785
SIZE: B
SCALE: NONE
SHEET 1 OF 2

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH.
©COPYRIGHT 2009 CINCH


Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.




9 CONTACTS




15 CONTACTS




21 CONTACTS




25 CONTACTS



31 CONTACTS



37 CONTACTS



51 CONTACTS

M83513/06-A 04

Connector Type
06 - Plastic Shell Plugs with Solder Cup Termination

07 - Plastic Shell Sockets with Solder Cup Termination

08 - Plastic Shell Plugs with Wire Leads

09 - Plastic Shell Sockets with Wire Leads

Insert Arrangements
(No. of Contacts)
A = 9
B = 15
C = 21
D = 25
E = 31
F = 37
G = 51

Wire Type (Use only for /08 & /09, otherwise omit)
01 - M22759/11-26-9, 18 inches, White
02 - M22759/11-26-9, 36 inches, White
03 - M22759/11-26-(), 18 inches, Color Coded
04 - M22759/11-26-(), 36 inches, Color Coded
05 - QQ-W-343, 25 AWG, 0.5 inch, Gold-Plated
06 - QQ-W-343, 25 AWG, 1.0 inch, Gold-Plated
07 - QQ-W-343, 25 AWG, 0.5 inch, Tin-Plated
08 - QQ-W-343, 25 AWG, 1.0 inch, Tin-Plated
09 - M22759/33-26-9, 18 inches, White
10 - M22759/33-26-9, 36 inches, White
11 - M22759/33-26-(), 18 inches, Color Coded
12 - M22759/33-26-(), 36 inches, Color Coded
13 - M22759/11-26-9, 72 inches, White
14 - M22759/11-26-(), 72 inches, Color Coded
15 - M22759/33-26-9, 72 inches, White
16 - M22759/33-26-(), 72 inches, Color Coded

* FOR OTHER OPTIONS, CONSULT FACTORY

UNITS **ENGLISH INCHES**

CATALOG DRAWING

UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS ARE IN INCHES

CINCH

1700 FINLEY RD
LOMBARD, IL. 60148

TITLE
DURA-CON ALL PLASTIC MICRO-D, SOLDER CUP AND WIRE TERMINATED

PRO/E DRAWING

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH.
©COPYRIGHT 2009 CINCH

CAD FILE NUMBER	DRAWING NUMBER	REV
M83513	M83513	1
CAGE IDENT NO. 71785	SIZE B	SCALE NONE

SHEET 2 OF 2

Downloaded from Arrow.com.