




CUSTOMER DRAWING



ORDER P/N SYSTEM:

MDT XXX STD 00X

CONNECTOR HEIGHT

XXX	L1	
225	0.35	NOT TOOLED
245	0.55	NOT TOOLED
275	0.80	TOOLED
320	1.45	TOOLED
420	2.45	TOOLED
580	3.95	TOOLED
850	6.65	TOOLED

MYLAR:


1:WIHT MYLAR
2:WIHTOUT MYLAR

NOTES:

1. MATERIAL:
TERMINAL: FREE CUTTING STEEL
2. FINISH:
TERMINAL:
PURE MATTE TIN PLATING 100u" THICKNESS MIN.;
UNDER PLATING: NICKEL PLATING 50u" THICKNESS MIN. OVERALL
3. PACKING IN TAPE AND REEL
4. MATERIAL SHOULD BE FULFILLED AMPHENOL SPEC# S-SN-002
5. ORDER P/N: SEE P/N SYSTEM

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1	CD---	FIRST RELEASE	MAR.11,2014	YH
2	CD0620	UPDATE DRAWING, ADD P/N	JUL.03,2014	YH
3	CD0887	UPDATE DRAWING, ADD P/N	Aug.04,2016	YH
4	CD0984	UPDATE DRAWING, ADD P/N	Feb.08,2017	YH
5	CD1192	UPDATE DRAWING, ADD P/N	Dec.27,2017	YH
6	CD1694	UPDATE DRAWING, ADD P/N	Apr.23,2019	YH



PCB RECOMMEND LAYOUT PATTERN



UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- 0.50 .XX +/- 0.25 .XXX +/- 0.10 FRACTIONS +/- ANGLES +/- 5° FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES (METRIC) (MM)		APPROVAL		DATE		Amphenol			
		DRAWN	Teng.Cao	Apr.23,2019					
		CHECKED	Ly.yi	Apr.23,2019					
		APPROVED							
DRAWING FILE :		INTERNAL\DRAWING\M.2\CMDTXXXSTD00X		TITLE					
				M.2 CONNECTOR STAND OFF					
				SIZE	DRAWING NO.			REV.	
				A3	C MDTXXXSTD00X			6	
				SCALE	NONE		SHEET 1 OF 1		