

KDT-ST 8 - Filler plug

3063976

<https://www.phoenixcontact.com/us/products/3063976>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Filler plug, material: PA, length: 20 mm, diameter: 8 mm



Commercial data

Item number	3063976
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF67
Product key	AF7CZX
GTIN	4046356301435
Weight per piece (including packing)	1.14 g
Weight per piece (excluding packing)	1.088 g
Customs tariff number	39174000
Country of origin	DE

KDT-ST 8 - Filler plug



3063976
<https://www.phoenixcontact.com/us/products/3063976>

Technical data

Notes

General	The filler plugs are used to seal unused cable sleeves.
---------	---

Product properties

Product type	Sealing plugs
--------------	---------------

Dimensions

Dimensional drawing	
Length	20 mm
Diameter	8 mm

Material specifications

Color	black (RAL 9005)
Material	PA

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP54 (Observe the assembly instructions)
Ambient temperature (operation)	-20 °C ... 80 °C

Mounting

Assembly note	IP54: for vertical sealing frame mounting/for horizontal sealing frame mounting (downward cable outlet direction).
---------------	--

KDT-ST 8 - Filler plug


3063976

<https://www.phoenixcontact.com/us/products/3063976>



Drawings

Dimensional drawing



Dimensional drawing

KDT-ST 8 - Filler plug

3063976

<https://www.phoenixcontact.com/us/products/3063976>



Classifications

ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	23111190

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

KDT-ST 8 - Filler plug



3063976
<https://www.phoenixcontact.com/us/products/3063976>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com