


214A032-4/42-0 Product Details

[Share](#) | [Print](#) | [Email](#)


214A032-4/42-0

Molded Parts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Molded Part Type = D Subminiature Boot
 - Family Name = 214A0
 - Straight
 - General Purpose Application
 - 10 Material Systems Code
- [View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 814072-000
 Active

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • Boot, Rectangular, Subminiature, Straight (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
---	--

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Molded Part Type = D Subminiature Boot • Family Name = 214A0 • Angle = Straight • Adhesive Description = General Purpose Pre-Coat Adhesive • Size = 32 <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Adhesive Pre-Coating = With <p>Dimensions:</p> <ul style="list-style-type: none"> • Cable Diameter Range (mm [in]) = 8.10 - 14.00 [0.319 - 0.551] • Connector Length (mm [in]) = 42.00 - 42.20 [1.654 - 1.661] • Connector Width (mm [in]) = 10.70 [0.421] <p>Body Features:</p> <ul style="list-style-type: none"> • Material = Polyolefin Flexible Modified <p>Housing Features:</p> <ul style="list-style-type: none"> • Material Systems Code = 10 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Material Code = 4 <p>Industry Standards:</p> <ul style="list-style-type: none"> • Government/Industry Qualification = No • Approved Standards = DEF Std 59-97 Issue 3 Type DA, MIL-I-81765/2 Class II, UL224 E85831 • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Environmental:</p> <ul style="list-style-type: none"> • Operating Temperature (°C) = -20 - +60 <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = General Purpose <p>Purchasing Information:</p> <ul style="list-style-type: none"> • Adhesive Code = 42 <p>Other:</p> <ul style="list-style-type: none"> • Brand = Raychem
---	--

- #### Corporate Information
- [About TE](#)
 - [Investors](#)
 - [News Room](#)
 - [Supplier Portal](#)
 - [Careers](#)
 - [Terms & Conditions](#)
 - [Privacy Policy](#)
 - [AODA Accessibility Policy](#)
 - [AODA Multi-Year Accessibility Plan](#)

- #### Quick Links
- [Distributor Inventory](#)
 - [Product Cross Reference](#)
 - [Documents & Drawings](#)
 - [Product Compliance Support Center](#)
 - [Site Map](#)

- #### Customer Support
- [Email or Chat With Us](#)
 - [Find a Phone Number](#)
 - [Knowledge Base](#)
 - [Manage Your Account](#)

Keep Me Informed



Feedback