



Front Panel, anodized with untreated edges, unshielded, screw assembly

SCHROFF



Other Views



Catalog Number: 30818-277
Back To Product

- Partial width front panel, Al, 2.5 mm
- Al, clear anodized, cut edges plain

Note:
Please order fixing material (sleeves, collar screws) separately, see Downloads-Mounting Hardware

Specification:

- IEC 60297-3-101
- IEEE 1101.1/10

Material and Surface Finish:
Al, Anodized, Untreated Edges

Assembly:
Screw on - Front Side

EMC Shielding:
Unshielded

Type:
Individual Components

Individual Component Type:
Front Panels

Standard pack quantity (SPQ):
Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.



Select product specifications before modifying or adding to project list or requesting a quote.

Height-U-defining

Width-HP-defining

[Clear Selection](#)

Quantity

Modify Product ▶

Add Item to Project List +

Documents

 Main Catalog - Front panels

Links

 Mounting Hardware

 Native CAD files

Technical Data	
Height mm	128.4
Qty	1 piece (SPQ 5)
B mm	40.3
Thickness mm	2.5
Height U	3
Width HP	8

Delivery Comprises:

Item	Quantity	Description
------	----------	-------------


Accessories



Collar screw, cross recess/slotted (M2.5x12.3), steel nickel plated, PU 100 pcs

21101-101


[Add Item to Project List](#) +



Quarter-turn fastener with knurled and slotted head, grey, PU 100 pcs

21101-849

[Add Item to Project List](#) +



Quarter-turn fastener with slotted head, grey, PU 100 pcs

21101-847

[Add Item to Project List](#) +



Sleeve, brass nickel-plated, PU 100 pcs

21100-660

[Add Item to Project List](#) +



Sleeve, brass, black, PU 100 pcs

21100-886


[Add Item to Project List](#) +



Sleeve, stainless steel, PU 100 pcs

21100-662


[Add Item to Project List](#) +



Sleeve, plastic, black, PU 100 pcs

21100-591


[Add Item to Project List](#) +



Quarter-turn fastener with slotted head, black, PU 100 pcs

21101-848


[Add Item to Project List](#) +



Sleeve, plastic, grey, PU 100 pcs

21100-464


[Add Item to Project List](#) +



Collar screw, Torx (M2.5x12.3), steel nickel plated, PU 100 pcs

21101-782


[Add Item to Project List](#) +



Collar screw, Torx (M2.5x12.3), steel black, PU 100 pcs

21101-783


[Add Item to Project List](#) +



Collar screw, knurled head long for LD (M2.5x12.3), brass nickel plated, PU 100 pcs

21101-909


[Add Item to Project List](#) +



Collar screw, knurled head short (M2.5x12.3),
brass nickel plated, PU 100 pcs

21101-
749

[Add Item to Project List](#) +



Quarter-turn fastener with knurled and
slotted head, black, PU 100 pcs

21101-
850

[Add Item to Project List](#) +



Collar screw, cross recess/slotted (M2.5x12.3),
steel black, PU 100 pcs

21101-
102

[Add Item to Project List](#) +

EXPLORE

- [About Us](#)
- [Services & Capabilities](#)
- [News & Events](#)
- [Newsletter Subscriptions](#)
- [Strategic Partnerships](#)
- [Investor Relations](#)

CONTACT

- [Customer Service](#)
- [Find a Sales Office or Distributor](#)
- [Global Locations](#)
- [Product Compliance & Certifications](#)
- [Partner Login](#)

DOWNLOAD

- [Download Center](#)
- [Reference Projects](#)
- [Videos](#)
- [Product Configurators](#)
- [Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

