




22759/43-14-2 Product Details

[Share](#) [Print](#) [Email](#)

Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

22759/43-14-2

22759/43-14-2

TE Internal Number: 217445-000

[Product Highlights](#) [View All](#)

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 14 AWG
- Voltage Rating = 600 VAC

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Documents](#)
Features
[Compliance](#)
Please Note:

Use the Product Drawing for all design activity

Product Type Features

 Cable Type [?](#) Spec 55

 Cable Style [?](#) Primary

Electrical Characteristics

Voltage Rating (VAC) 600

Dimensions

Conductor Outer Diameter (mm [in]) 1.70 [0.067]

Body Features

Wire Size (AWG/CM) 14 AWG

Conductor Type Silver-Coated Copper

Wire Color Red

Nominal Outside Diameter (mm [in]) 2.39 [0.094]

Wire Diameter (mm [in]) 2.39 [0.094]

Configuration Features

Number of Conductors 1

Industry Standards

Government/Industry Qualification

No

 RoHS/ELV Compliance [?](#) RoHS compliant, ELV compliant

 Lead Free Solder Processes [?](#) Not reviewed for lead free solder process

RoHS/ELV Compliance History Always was RoHS compliant

Conditions for Usage

Temperature Range (°C) -65 – +200

 Wire Size - Details 14 AWG 1.94 mm², 0.003 in², 19 x 27 AWG

Operation/Application

Application Airframe - Medium Weight

Packaging Features

Wire Source United States

Other

Brand Raychem

Node Classification Hook Up Wire

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)
[View Part in Product Feature Selector](#)
[Check for Tooling](#)
[Feedback](#)
Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms of Use of TE.com](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)
- [Terms & Conditions of Sale](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed
