

1-Port USB Wall Charger with Quick Charge 3.0 Technology

MODEL NUMBER: **U280-W01-QC3**



Fast charger with auto-sensing Quick Charge 3.0 USB-A port charges a single mobile device at a time. Smartphones, tablets and other devices compliant with Quick Charge 3.0 charge up to 4x faster than conventional USB devices.

Description

The U280-W01-QC3 1-Port USB Wall Charger lets you quickly and safely charge a USB-powered mobile device. Recommended for smartphones, tablets, digital cameras, MP3 players and other USB devices, this wall/travel charger features one QC 3.0 Quick Charge port for rapid charging of QC 3.0-compliant devices—up to four times faster than normal USB charging.

The USB-A port features built-in auto-sensing technology that detects the connected device and automatically adjusts to the appropriate power level up to 5V 2.4A, perfect for fast-charging tablets and e-readers. A front LED indicates successful charging.

To charge your USB device, simply connect the unit to a NEMA 1-15R, 5-15R or 5-15/20R AC outlet, and connect your device to the available USB port. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity.

Compactly designed for easy carrying in a backpack, purse, suitcase or laptop bag, the U280-W01-QC3 comes with international plug adapters for Europe, Australia and the United Kingdom, so you can use it almost anywhere. The NEMA 1-15P plug folds into the unit to protect it and other items in your bag from damage.

Features

Charges a Mobile Device at Quick Charge 3.0 Speeds

- Recommended for smartphones, tablets, digital cameras, MP3 players and other USB devices
- Quick Charge 3.0 Class A 5/9/12V technology

Highlights

- Quick Charge 3.0 Class A 5/9/12V technology
- Built-in auto-sensing technology for non-Quick Charge devices
- Protects against overheating, overcurrent and overcharging
- Compact design fits into backpacks, purses and laptop bags
- Works with any NEMA 1-15R, 5-15R or 5-15/20R AC outlet

Package Includes

- U280-W01-QC3 1-Port USB Wall Charger with Quick Charge 3.0 Technology
- (3) International plug adapters (EU, AU, U.K.)
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- QC 3.0-compliant devices charge up to 4x faster than conventional USB charging
- Auto-sensing USB port detects non-Quick Charge device and adjusts to proper power level up to 5V, 2.4A
- Protects against overheating, overcurrent and overcharging
- LED indicates successful charging

Convenient Charging Almost Anywhere

- Compact design fits into backpacks, purses and laptop bags
- Works with any NEMA 1-15R, 5-15R or 5-15/20R AC outlet
- European, Australian and U.K. plug adapters included for international power outlets

Specifications

OVERVIEW	
UPC Code	037332197405
Product Type	Wall Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 240V AC
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
OUTPUT	
Overload Protection	Yes
CHARGING	
Charging Ports / Amps	3A / 2A / 1.5A
Number of Charging Ports	1
Total Charging Amps	3A
Charging Method	USB
Charging Ports Detail	3.6V~6.5V/3A, 6.5V~9V/2A, 9V~12V/1.5A
Charging Port Type	USB A (FEMALE)
Charging Method Detail	Quick Charge 3.0
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	White
Shipping Dimensions (hwd / cm)	4.83 x 11.18 x 15.75
Shipping Dimensions (hwd / in.)	1.90 x 4.40 x 6.20
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.50
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	5% to 90% RH, Non-Condensing
CONNECTIONS	
Ports	1
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Quick Charge Compliant	3.0
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Approvals	UL Listed
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>