

4-in-1 Ultra-Compact Inverter with Mobile Charging

MODEL NUMBER: **PV4IN1**



Highlights

- Ideal for smartphones, tablets, laptops, GPS units and MP3 players
- Includes a 2.1A USB-A charging port and a retractable 24 in. Micro-USB charging cord
- Comes with handy travel pouch and four charging adapters
- Durable plastic housing withstands rigors of travel

Package Includes

- PV4IN1 Mobile Charger
- Travel Pouch
- Four Charging Adapters
- Owner's Manual

Features four different inputs to charge and power mobile devices and portable electronics from a standard wall socket, a vehicle's 12V CLA socket, a USB power source or a 9V battery.

Description

The PV4IN1 charges and powers mobile devices such as phones or tablets anywhere, any time. This inverter includes a fold-down plug to charge directly from an AC wall outlet, a plug to charge from a vehicle's 12V CLA outlet, a 5V USB-A input cord and a 9V battery input for short-term emergency power (battery not included).

To charge your device, just connect it to the USB output port or the retractable 24 in. Micro-USB charging cord. To make it easy to charge any mobile device, the PV4IN1 includes four charging adapters: Apple® 30-pin, Nokia® 2 mm, Sony® PSP® and USB Mini-B. For on-the-road portability, the included travel pouch holds the inverter and the adapters.

Features

4 Ways to Power and Charge Multiple Devices

- Powers and charges smartphones, laptops, tablets, GPS units or MP3 players
- Fold-down NEMA 1-15P plug provides charging power to the unit directly from an AC wall outlet
- CLA plug lets you convert 12V DC power to standard 120V power from the battery in a car, truck, RV or boat
- USB-A input allows the unit to draw power from a USB source, such as a computer or a USB wall socket
- 9V battery input can be used as a short-term emergency power source (battery not included)

2 Output Ports for Easy Charging of Any Mobile Device

- Built-in connections provide a USB-A charging port and a 24 in. retractable Micro-USB charging cord
- Delivers a total of 2.1A to all devices being charged at the same time
- Charge a wide variety of devices with the four included adapters: Apple® 30-pin, Nokia® 2 mm, Sony® PSP® and USB Mini-B; the adapters connect directly to the Micro-USB charging cord
- LED indicates when the unit is plugged in and ready to provide power

Ready for Travel and Made to Last

- Convenient travel pouch keeps the inverter and all adapters together and close at hand
- Durable plastic housing stands up to the rigors of travel for years of dependable use
- No maintenance required

Specifications

OVERVIEW	
UPC Code	037332191823
INPUT	
Input Connection Type	12VDC cigarette lighter input plug connection
Voltage Compatibility (VDC)	12
Input Plug Type	NEMA 5-15P
OUTPUT	
Frequency Compatibility	60 Hz
Pure Sine Wave Output	No
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(1) 5-15R
Continuous Output Capacity (Watts)	100
BATTERY	
DC System Voltage (VDC)	5V (USB type A), 9V Battery, 12V (CLA Adapter)
CHARGING	
Charging Ports / Amps	(1) 2.1A
PHYSICAL	
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	2.00 x 3.90 x 5.90
Shipping Dimensions (hwd / cm)	5.08 x 9.91 x 14.99
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	1.160 x 3.480 x 4.570
Unit Dimensions (hwd / cm)	2.95 x 8.84 x 11.61
Unit Weight (lbs.)	.55
Unit Weight (kg)	0.25



1000 Eaton Boulevard
Cleveland, OH 44122
United States

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.