

Shop Online ▶ Fasteners ▶ Standoffs ▶ Double Female ▶ 2124-632-SS

 **RAF Electronic Hardware**

2124-632-SS - Standard Stainless Steel Female-Female Standoff

Standard Hexagon female-female standoff manufactured from Stainless Steel with an 0.25 Inch outside diameter. Product 2124-632-SS is designed with a 1.75 Inch long shaft and 6-32 threads.

 **Download CAD**

StandardMetric

[Print Spec Sheet](#)

Body Texture	Plain
Brand	RAF
Display Name	2124-632-SS
Finish	None
Length L	1.75 in
Material	Stainless Steel
Measurement Units	Standard
Outside Diameter	0.25 in
SKU	2124-632-SS
Shape	Hexagon
Standoff Option	Standard
Thread Size	6-32
Thread Type	Female, Female

You May Also Like



RAF
Standoffs Swage Mount

7725-B-632-SS - Standard Stainless Steel Smooth Shank Swage Mount Standoff

Limited Availability ●


Request a quote



ACCURATE SCREW
Standoffs Swage Mount

J72060RPhl - Standard Phenolic (Linen) Smooth Shank Swage Mount Standoff

Request a quote



RAF
Standoffs Double Female

2678-832-AL - Standard Aluminum Female-Female Standoff

Limited Availability ●

Request a quote

In-Stock ●[Check Stock](#)

Finish*
None

Request a Quote

Quantity
1

Add to Quote

Need more information? [Contact us](#) for further questions.

To continue with your selected configuration, please submit a quote through the cart. Our team will process your request and contact you with quoted pricing.

Related Resources

SAE (inch) Dimensions for Fasteners

 [BUYING GUIDE](#)

Glossary

 [GLOSSARY](#)

Metric Bolt Conversion

 [GUIDE](#)

RAF Quick Turn Service

 [BROCHURE](#)

View More Resources



COMPANY

[About MW Components](#)

[Our Companies](#)

[Privacy Policy](#)

[Your Privacy Preferences](#)

[Manage Cookies](#)

[Data Privacy Request](#)

[Terms of Use](#)

RESOURCES

[Certifications](#)

[FAQs](#)

[Industries](#)

[Materials](#)

[Reviews](#)

[Standard Terms & Conditions](#)

[Return Policy & Promotion Terms](#)

TOP PRODUCTS

[Compression Springs](#)

[Extension Springs](#)

[Captive Screws & Assemblies](#)

[Bolts](#)

[Bellows / Couplings](#)

[Shims](#)

CONNECT

[Contact Us](#)

[Request A Quote](#)

[Ask An Expert](#)

[Careers](#)

STAY INFORMED

Subscribe

WEBSITE FEEDBACK?

Share Your Feedback

MW Components is a proud member of [IFI](#), [NESMA](#), [SMI](#) and [CASMI](#).

Sales Inquiries: **704.837.0331**

Corporate Address: 3426 Toringdon Way # 400,
Charlotte, NC 28277



MW Components' Hyperco brand is a Competition Partner and supplier to the NASCAR Cup Series.