
# Specification Sheet

Part Number: MB4A0H4



For use with HellermannTyton T18 - T50 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 1.1 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.

Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, Black, 500/pkg

| | |
|---|---|
| Article Number | 151-28406 |
| Type | MB4A |
| Color | Black (BK) |
| Quantity Per | pack |
| Product Description | MB4A adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options. |

Downloaded from Arrow.com.

| | |
|---|---|
| Short Description | Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, Black, 500/pkg |
| Global Part Name | MB4A-PA66-BK |
| Length L (Imperial) | 1.12 |
| Length L (Metric) | 28.5 |
| Fixation Method | Adhesive |
| Width W (Imperial) | 1.12 |
| Width W (Metric) | 28.5 |
| Cable Ties | T18 - T50 |
| Height H (Imperial) | .22 |
| Height H (Metric) | 5.6 |
| Cable Tie Width Max (Imperial) | 0.18 |
| Cable Tie Width Max (Metric) | 4.6 |
| Mounting Hole Diameter D (Imperial) | 0.18 " |
| Mounting Hole Diameter D (Metric) | 4.6 mm |
| Mounting Hole Centers (Imperial) | 0.8 |

Downloaded from Arrow.com.

| | |
|---|---|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Adhesive | Synthetic rubber with base of polyethylene foam |
| Flammability | UL 94 V-2 (excluding adhesive) |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor and Outdoor Use |
| Adhesive Operating Temperature | 0°F to +150°F (-18 °C to +66 °C) |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| BABA Compliant | YES |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |

Downloaded from Arrow.com.

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.



Downloaded from Arrow.com.