

2SJ211

[Provide feedback](#) [Print this page](#) TEXT SIZE
S M L

- Products
- Discrete
- Power MOSFETs
- Power MOSFETs for General Switching
- 2SJ211

Overview Documentation Design Support

- Product Spec Order Information Package & Packing

Product Spec

Downloadable	-	Ciss (pF) typ.	-
Configuration	-	ID (A)	-0.2
Configuration	-	V _{GSS} (V)	-
V _{DS} (V) min.	-100	Nch/Pch	Pch
R _{DS} (ON) (ohm) typ. @4V[4.5V]	-	Application	-
R _{DS} (ON) (ohm) max. @4V[4.5V]	-	Package name	-
R _{DS} (ON) (ohm) typ. @2.5V[1.8V]	-	VP Ready	-
R _{DS} (ON) (ohm) max. @2.5V[1.8V]	-	V _{DSS} (V)	-100
R _{DS} (ON) (ohm) typ. @10V[8V]	-	toff (μs) typ.	-
R _{DS} (ON) (ohm) max. @10V[8V]	20	QG (nC) typ.	-
Performance	-	Feature	-
Description	-	Remarks	-
Features	-	Production Status	Mass Production
P _{ch} (W)	-	Ordering Condition	-

[Back To Top](#)

Order Information

Orderable Part No.	Production Status.	Packing	Environmental	remark
2SJ211(0)-T1B-A	Mass Production	-	Pb free	-
2SJ211-L-A	Mass Production	-	Pb free	-
2SJ211-T2B-AT	Mass Production	-	Pb free	-
2SJ211-T1B-AT	Mass Production	-	Pb free	-
2SJ211-T1B-A	Mass Production	-	Pb free	-
2SJ211-T2B-A	Mass Production	-	Pb free	-
2SJ211-L-AT	Mass Production	-	Pb free	-
2SJ211-L	EOL	-	-	-
2SJ211-T2B	EOL	Tray	-	-
2SJ211-T1B	EOL	Tray	-	-

[Back To Top](#)

Package & Packing

[p3c3-95-121](#) [fig1082e](#)

Package	
Renesas code	PLSP0003ZD-A
Previous code	P3C3-95-121
JEITA code	SC-59
Name	MM
Terminal count	3
Terminal pitch (mm)	0.95
Dimensions (mm)	2.9x1.5
Mass (g) [Reference value]	0.012
Mounting height (mm) [MAX]	1.4
Terminal material - Base	52Alloy
Terminal material - Surface	Sn-Bi or Sn
Drawing Link	p3c3-95-121
Mount pad	fig1082e

Packing	
Packing Tape No dry pack	H2275
Container Tape	H0803

[Back To Top](#)