





[Labels](#) / [Circuit Board Labels](#) / [Not for Wash Polyester Labels](#) /

BMP61 BMP71 TLS 2200 WorkHorse Polyester Labels



BMP61 BMP71 TLS 2200 WorkHorse Polyester Labels

Part Number:

PTL-9-423

Label/Tape Size:

0.2 in H x 0.65 in W

Material:

Polyester

For Use with Printer:

BMP®61 Labeling System, BMP®71 Label
Printer, TLS 2200® Thermal Labeling
System, TLS-PC LINK™ Thermal Labeling
System

Material Number:

B-423

Color:

White

[ADD TO CART](#)

1

[Add To Favorites](#)

OVERVIEW

Permanent Polyester (B-423) is ideal for electronic PCB and component identification, bar code labels, rating plates and solar panel identification.

- Glossy white finish with permanent acrylic is thermal transfer printable
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted
- Meets requirements of a halogen-free material per DIN VDE 0472 part 815
- Service temperature of -94 to 230° F (-70 to 110° C)

SPECIFICATIONS

Material Number	B-423
Catalog Page #	348
Dimensions	0.2 in H x 0.65 in W
UOM	Roll of 750 Labels
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Label/Tape Size	0.2 in H x 0.65 in W
Maximum Service Temperature °F	230 °F
Minimum Service Temperature °F	-94 °F
Pre-Printed Areas on Label	Colored Write-On Area
Printable Area Dimensions	0.2 in H x 0.65 in W
Printable Area Height	0.2 in
Printable Area Width	0.65 in
Product Number	18333
UPC	662820183334
Quantity per Roll	750
Quantity per Row	1
Secondary Label Included	Secondary Label is Not Included
Thickness	0.003 in
Trade Name	BMP®61 BMP®71 TLS 2200® TLS-PC Link™ WorkHorse®
Adhesive Type	Acrylic
Applications	Asset Tracking, Barcode Labeling, Circuit Board ID - Through Hole Top, Component & Equipment ID, General & Industrial ID, Rating Plates
Color	White
For Use with Printer	BMP®61 Labeling System, BMP®71 Label Printer, TLS 2200® Thermal Labeling System, TLS-PC LINK™ Thermal Labeling System
Header	No Header
Label/Media Format	Roll
Language	No Text
Material	Polyester
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Rectangle



Solutions

- Floor Marking Guide
- GHS Label Compliance
- Lockout Tagout Compliance
- Arc Flash Labeling Requirements
- Cable and Wire Label Options
- Product and Barcode Labeling
- Brand Protection Solutions

Services

- Lockout Tagout Services
- Arc Flash Services
- Confined Space Services
- Visual Workplace Services
- Hazcom GHS Services
- Software Programming & Integration
- Label Template & File Conversion
- Printer Use & Training
- Printer Preventative Maintenance
- Toll and Custom Coating
- Authentication & Tracking Services

Help

- Contact Us
- Knowledge Center
- Printer Drivers & Firmware
- Brady Software Updates
- Safety Data Sheets
- Technical Data Sheets
- WEEE-RoHS Compliance
- Product Certification
- Printer Registration

Resources

- Find a Distributor
- Printer Selection Tool
- Label Selection Tool
- Digital Catalog
- Request a Catalog
- Interactive Facility Map

Corporate

- About
- Careers
- Investors
- Privacy Policy
- Terms and Conditions
- Terms of Use
- ISO Certification

Other

- Brady Sites
- Distributor Portal
- International Sites
- Safety Services
- Software Smart ID
- Brand Protection Solutions


Resources

- Press Releases
- Request a Catalog
- Find a Distributor
- Log Out

Contact

6555 W. Good Hope Rd. Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2018 Brady Worldwide, Inc.