
**Part Number :** 2012002081
**Product Description :** Spot-On Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, 8 Circuits, Black
**Series Number :** 201200
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

2012002081_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

2011960000-A00.pdf

2011960000-A01.pdf

2012009200-200.pdf

2012000000-PS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 201200 |
| Description | Spot-On Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, 8 Circuits, Black |
| Application | Wire-to-Board |
| Component Type | Receptacle |
| Keyword | Spot-On 2.0 |
| Product Name | Spot-On |
| UPC | 191128252348 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Polybutylene Terephthalate (PBT) |
| Net Weight | 828.000/mg |
| Number of Rows | 1 |

Downloaded from Arrow.com.

| | |
|---|---|
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 2.00mm Pitch, Spot-On Vertical Single Row Headers with Potting Capability | 201201 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| Spot-On 2.0 Crimp Terminal, Female, Matte Tin (Sn) Plating, 26-22 AWG | 2011956000 |
| Spot-On Terminal Position Assurance (TPA) Wire-to-Board Retainer, 2.00mm  Pitch, 8 Circuits, Gray | 2011964080 |



Downloaded from Arrow.com.