

# 3M™ Bumpon™ Resilient Rollstock SJ5808 Black

## R30FL, configurable product

Part Number SJ5808



Overview

Specifications

Details

Resources



- All 3M™ Bumpon™ Protective Products feature a urethane composition **More...**

[View Images](#)

[View all details](#)

[View Legal Disclaimer](#)

## Specifications

Attribute Name	Value
Adhesive Type	Natural Rubber (R30)
Applications	Cushioning Spacer , Cushioning Stop , Gasketing , Notebook Computer Non-Skid Feet , Protective Non-Skid Feet , Surface Protection , Surface Protection for Sub-Assembly Racks
Availability	Make to Order
Backing Material	Polyurethane
Color	Black
Hardness	72 Shore M
Height-Thickness Range	0.100 - 0.199 in
Height-Thickness Range (metric)	3.0 - 3.9 mm
Market Segment	All Markets , Automotive , Cabinetry , Electronics
Primary Liner	Translucent Polyester Film
Product Form	Rollstock
Shape	Rollstock

Thickness	0.125 Inch
Thickness (Metric)	3.2 mm
Trademark	3M

## Details

- All 3M™ Bumpon™ Protective Products feature a urethane composition
- Easy application with 3M pressure-sensitive adhesives
- High skid resistance
- Won't scratch or stain surfaces
- Reduces vibration and noise
- Will not crack or harden

3M™ Bumpon™ Resilient Rollstock SJ5808 is a self adhesive rubber bumper designed to be used as feet, stops and spacers. The rollstock format is excellent for die cut shapes with various thickness requirements.

## Resources

### Brochure

[3M™ Bumpon™ Protective Products \(PDF, 374.6KB\)](#)

### Data Sheet

[3M™ Bumpon™ Protective Products Resilient Rollstock, Opaque \(PDF, 276.8KB\)](#)

## Legal Disclaimer

### Product Disclaimer

- The technical information and data shown on this page should be considered representative or typical only and should not be used for specification purposes.
- 3M products shown on this website may not be available in all geographic regions or may not be available at this time. Please contact your local sales representative to determine product availability.

## 3M United States

### HELP

[Help Center](#)

[Site Map](#)

### REGULATORY

[SDS Search](#)

[Transport Information Search](#)

[RoHS & REACH Information Search](#)

[CPSIA Certification Search](#)

[California Supply Chains Act Disclosure \(PDF, 84KB\)](#)

### NEWS

[News Center](#)

[Particles by 3M](#)

[Press Releases](#)

### ABOUT US

[About 3M](#)

[3M Careers](#)

[Investor Relations](#)

[Partners & Suppliers](#)

[Government Customers](#)

[Sustainability](#)

[3Mgives](#)

[UK Modern Slavery  
Act Statement \(PDF,  
169KB\)](#)

[More Regulatory &  
Compliance  
Information](#)

SEARCH 3M



FOLLOW US



**United States** [English](#)



[Legal](#) | [Privacy](#) | [DMCA](#)  
© 3M 2018. All Rights Reserved.

The brands listed above are trademarks of 3M.