

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/6/21	
A		ADDED PAGE 3	5/6/21	LH/RC
B		UPDATE PAGE3	10/25/21	LH/RC
C		CORRECTED OVERALL LENGTH ON PG 1	9/11/23	SS





LABEL FOR CABLE

SPECIFICATIONS:

Connector:

P1= Mini FAKRA Code see Page2 , Jack, Straight, 30u" Gold Plated, UL94-V0

P2~P5= FAKRA Code see Page3, Plug, Straight, 30u" Gold Plated, UL94-V0

Cable:

Coaxial Cable+AL+Braid, O.D: .130" [3.3mm], Jacket Color: Black

Electrical:

Impedance: 50 Ohm

Temperature Rating:

-40°C to +105°C

Electrical Test:

All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	LH	5/6/21
CHECKED	RC	5/6/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: MINI FAKRA JACK STRAIGHT 2*2 TO FAKRA PLUG
*4 STRAIGHT , OD 3.3 CABLE, 3.937" [100mm] LONG

SIZE	PART NO.	REV.
X	CA-BM04XJ-4FPX-0.3	C

REF: S00013T | SCALE: NTS | SHEET 1 OF 3

Downloaded from Arrow.com.


Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				


APPROVED: _____


DATE: _____ TITLE: _____


CA-BM04XJ-4FPX-0.3


CODING A	CODING B	CODING C	CODING D	CODING E
BLACK	PURE WHITE	LIGHT BLUE	CLARET VIOLET	MAY GREEN














CODING F	CODING Z
NUT BROWN	WATER BLUE





All Coding



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	LH	5/6/21
CHECKED	RC	5/6/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: MINI FAKRA JACK STRAIGHT 2*2 TO FAKRA PLUG *4 STRAIGHT , OD 3.3 CABLE, 3.937" [100mm] LONG

SIZE	PART NO.	REV.
X	CA-BM04XJ-4FPX-0.3	C

REF:	SCALE:	SHEET
S00013T	NTS	2 OF 3

Downloaded from Arrow.com.








Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				

APPROVED: _____

DATE: _____ TITLE: _____

CA-BM04XJ-4FPX-0.3

Fakra Plug

Coding	A	B	C	D	E	F	Z
Plug							
Color	Black	White	Blue	Bordeaux Violet	Green	Brown	Water Blue

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	LH	5/6/21
CHECKED	RC	5/6/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: MINI FAKRA JACK STRAIGHT 2*2 TO FAKRA PLUG
*4 STRAIGHT , OD 3.3 CABLE, 3.937" [100mm] LONG

SIZE	PART NO.	REV.
X	CA-BM04XJ-4FPX-0.3	C

REF:	SCALE:	SHEET
S00013T	NTS	3 OF 3

Downloaded from Arrow.com.