

Network Cable Continuity Tester for Cat 5/Cat6/Cat6a, Phone, USB and Coax Cable Assemblies

MODEL NUMBER: T014-001



Highlights

- Combines main tester unit and removable remote tester unit
- Tests multiple types: RJ11, RJ45, USB, BNC
- Tests cable lengths up to 600 ft.
- LEDs indicate 9V battery status at a glance
- Includes convenient carrying case

Package Includes

- T014-001 Network Cable Continuity Tester
- BNC to RJ11 jumper cable
- Carrying case
- Owner's manual

Tests Cat5e, Cat6, Cat6a, telephone, USB and coax cable connections with the press of a button. Essential for cable installers or anyone in the telecom or LAN environments.

Description

The all-in-one T014-001 Network Cable Continuity Tester is an essential tool for cable installers or anyone working in telecom or LAN environments. It allows you to test wiring continuity for Cat5, Cat6, Cat6a, telephone, USB and coax cable assemblies at the press of a button. A combination of main tester unit and removable remote tester unit, the T014-001 identifies crossed wires, short circuits and open circuits in cables up to 600 ft. A BNC to RJ11 adapter is included for testing BNC cable. When not in use, the two-piece T014-001 can be stored in its handy carrying case. Battery status LEDs let you know when the 9V battery (sold separately) needs to be replaced.

Features

Essential Tool for Cable Installers or Telecom/LAN Personnel

- Tests Cat5, Cat6, Cat6a, telephone, USB and coax cable assemblies
- Combines main tester unit and removable remote tester unit
- Identifies crossed wires, short circuits and open circuits
- Tests multiple types: RJ11, RJ45, USB, BNC
- Tests cable lengths up to 600 ft.

Designed to Make Your Work Easier

- Includes BNC to RJ11 adapter for testing BNC cable
- Powered by 9V battery (sold separately)
- LEDs indicate battery status at a glance
- Stores away in convenient carrying case

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|--|
| UPC Code | 037332189929 |
| Accessory Type | Cable Tester |
| Technology | Cat5/5e; Cat6; Cat6a; USB 2.0 (High Speed); Coax |
| Accessory Class | USB Accessories |
| CONNECTIONS | |
| Side A - Connector 1 | RJ45 (FEMALE) |
| Side B - Connector 1 | RJ45 (FEMALE) |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 7.24 x 4.33 x 1.77 |
| Shipping Dimensions (hwd / cm) | 18.39 x 11.00 x 4.50 |
| Shipping Weight (lbs.) | 0.51 |
| Shipping Weight (kg) | 0.23 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.