Part Number : 2219602211
Product Description : PowerWize-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Female, Single Row, 1000.00mm Length, 2 AWG, 2 Circuits, Blue
Series Number : 221960
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2219602211_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	221960
Description	PowerWize-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Female, Single Row, 1000.00mm Length, 2 AWG, 2 Circuits, Blue
Assembly Configuration	Single Ended Connector
Connector to Connector	PowerWize-to-Pigtail
Product Name	PowerWize
Type	Discrete Wire Assembly
UPC	196823228001

Electrical

Current - Maximum per Contact	120.0A
Voltage - Maximum	300V AC

Physical

Cable Length	1000.00mm
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Blue
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold

Downloaded from Arrow.com.

Material - Plating Termination	Silver
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	123.772/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	19.06mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10198
Wire Size (AWG)	2

Mates With / Use With

Mates with Part(s)

Description	Part Number
PowerWize 6.00mm, 2-circuit, Screw Mount, Mechanical Keying Option B, Color Coded Blue, Vertical Header, Tray	2119370003

Downloaded from Arrow.com.