

4-Port USB 2.0 USB over Cat5 Hub with 3 local Ports and 1 Remote Port, TAA

MODEL NUMBER: **U224-1R4-R**



Description

Tripp Lite's U224-1R4-R is a kit that includes a 3-port USB 2.0 local transmitter unit, and a 1-Port USB 1.1 remote receiver unit. Connect up to 3 USB 2.0 devices to the local transmitter, while extending an additional USB 1.1 peripheral up to 150-ft. (45.72 m) from your computer. Simply plug the transmitter into the USB port on your computer, connect your USB peripherals, and run Cat5e/Cat6 cable up to 150-ft. (45.72 m) to the remote receiver unit and connected device. Plug-and-play; no software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Local transmitter unit features 3 USB 2.0 ports
- Remote receiver unit features 1 USB 1.1 port
- Locate a USB 1.1 peripheral up to 150-ft. (45.72 m) from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332146694
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
Technology	USB 2.0 (High Speed); USB

Highlights

- Local transmitter unit features 3 USB 2.0 ports
- Remote receiver unit features 1 USB 1.1 port
- Locate a USB 1.1 peripheral up to 150-ft. (45.72 m) from your computer
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 3-port USB 2.0 local transmitter unit
- 1-port USB 1.1 remote receiver unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 2.0
PHYSICAL	
Color	Black
Receiver Unit Height (in.)	0.9
Receiver Unit Width (in.)	1.8
Receiver Unit Depth (in.)	2.6
Shipping Dimensions (hwd / cm)	5.84 x 14.99 x 22.61
Shipping Dimensions (hwd / in.)	2.30 x 5.90 x 8.90
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Transmitter Unit Depth (in.)	3.3
Transmitter Unit Height (in.)	0.9
Transmitter Unit Width (in.)	2.4
CONNECTIONS	
Ports	4
Side A - Connector 1	USB A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>