



Part Number : [1731120397](#)

Product Description : FCT High Power Contact, Female, Straight, PCB Through Hole, 0.50µm Gold Mating Plating, 5.00µm Tin Termination Plating, Split Tine, 40.0A, 10-12 AWG

Series Number : 173112

Status : Active

Product Category : D-Sub Contacts

Engineering Number : FMP139S115

---

## Documents & Resources

### Drawings

[Drawing 1731120397\\_sd.pdf](#)


### Specifications

[Packaging Specification 1731120008-PK-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Female, Straight, PCB Through Hole, 0.50µm Gold Mating Plating, 5.00µm Tin Termination Plating, Split Tine, 40.0A, 10-12 AWG
Contact Type	High Power
Magnetic	Yes
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Mixed Layout
UPC	191128209588

### Electrical

Current - Maximum per Contact	40.0A
-------------------------------	-------

### Physical

Durability (mating cycles max)	200
Gender	Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	1.600/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	0.500µm
Plating min - Termination	5.000µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Through Hole
Wire Size (AWG)	10, 12

---

### Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

---

### Application Tooling

#### Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>

---

This document was generated on Jul 28, 2024