Product data sheet
Characteristics

AR8645
Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 10"W, Double-Sided with Doors

Product availability: Stock - Normally stocked in distribution facility



Overview

Presentation	This 10” wide, high capacity vertical cable manager for 2 and 4 Post open frame racks features a do

Main

Product or Component Type	Cable organizer
Provided equipment	Doors Installation guide Mounting Hardware 3 x Midspan brackets

Complementary

Mounting Mode	Not rack-mountable
Color	Black
Height	84.02 In (2134 mm)
Width	10.0 In (253 mm)
Depth	26.0 In (660 mm)
Net Weight	75.0 Lb(US) (34 kg)

Environmental

Product Certifications	UL Listed

Ordering and shipping details

Category	80230-IG SEBA TO SEUSA
Discount Schedule	BMS1
GTIN	731304291596
Returnability	No
Country of origin	US

Downloaded from Arrow.com.

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	16.0 In (40.6 cm)
Package 1 Width	90.04 In (228.7 cm)
Package 1 Length	32.5 In (82.6 cm)
Package weight(Lbs)	95.02 Lb(US) (43.1 kg)

Environmental data

Recyclability potential, in %	95
Total lifecycle Carbon footprint	151 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	144.3672555759853
Carbon footprint of the manufacturing phase [A1 to A3]	144 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	3.652250379726597
Carbon footprint of the distribution phase [A4]	4 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0
REACh free of SVHC	Yes
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	3.2112239187784795
Carbon footprint of the end-of-life phase [C1 to C4]	3 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Carbon footprint (kg CO2 eq, Total Life cycle)	151
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
REACh Regulation	Free of Substances of Very High Concern above the threshold
EU RoHS Directive	Compliant
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	24

Product Life Status : Commercialised

Downloaded from Arrow.com.