

462A421-51/86-0 Product Details

 [Share](#)  [Print](#)  [Email](#)



 **Active**

Molded Parts

462A421-51/86-0

462A421-51/86-0 

TE Internal Number: 233776-000

Product Highlights [View All](#)

- SC-X15112
- Molded Part Type = Breakouts/Transitions
- Wire/Cable Outside Diameter = 8.00 mm, 9.00 mm, 10.00 mm, 11.00 mm, 12.00 mm
- Molded Part Shape = Slimline, One to Three Cables
- Operating Temperature = -55 - 105 °C

[Pricing & Availability](#) 

[Request Sample](#) 

[Add to My Part List](#) 

[Buy Product through Distributor](#) 

[Feedback](#)

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Molded Part Type	Breakouts/Transitions
Molded Part Shape	Slimline, One to Three Cables
Adhesive Description	High Performance Pre-Coat Adhesive
Mechanical Attachment	
Adhesive Pre-Coating	With
Dimensions	
Wire/Cable Outside Diameter (mm [in])	8.00 [0.310], 9.00 [0.350], 10.00 [0.390], 11.00 [0.430], 12.00 [0.470]
1st Branch/Leg Range (mm [in])	8.00 – 10.00 [0.310 – 0.390]
2nd Branch/Leg Range (mm [in])	8.00 – 10.00 [0.310 – 0.390]
3rd Branch/Leg Range (mm [in])	8.00 – 10.00 [0.310 – 0.390]
Body Features	
Transition Type	One to Three Cables
Housing Features	
Material Systems Code 	20

Configuration Features	
Material Code	51
Number of Branches/Legs	3
Industry Standards	
Government/Industry Qualification	No
Approved Standards	SC-X15112
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Environmental	
Operating Temperature (°C)	-55 – +105
Purchasing Information	
Adhesive Code	/86
Other	
Adhesive Options	/86 Precoat, -55°C to +105°C (-67°F to +221°F)
Brand	Raychem

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

